



## 3801 - MALE STUD, BSP PARALLEL METRIC AND UNF



<b>maximum working pressure</b>	30 bar 3 MPa 435 psi
<b>working temperature</b>	-25 to 150 °C -13 to 302 °F 248 to 423 °K
<b>vacuum capability</b>	755 mm Hg
<b>body</b>	STAINLESS STEEL 316L
<b>'O'-rings</b>	FKM
<b>collar</b>	STAINLESS STEEL 316L
<b>sealing washer</b>	STAINLESS STEEL 316L

Part Nb	ØD (MM)	C	F (mm)	(mm)	H (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
3801 04 10	4	G1/8	13	3	16.5	.009
3801 04 19	4	M5x0,8	10	2.5	17	.005
3801 06 10	6	G1/8	13	4	18	.01
3801 06 13	6	G1/4	17	4	18	.015
3801 06 19	6	M5x0,8	13	2.5	20.5	.01
3801 08 10	8	G1/8	15	5	19	.013
3801 08 13	8	G1/4	17	5	20.5	.017
3801 08 17	8	G3/8	21	6	20	.027
3801 10 13	10	G1/4	19	7	25	.025
3801 10 17	10	G3/8	21	7	25	.034
3801 12 13	12	G1/4	21	7	27	.03
3801 12 17	12	G3/8	21	9	26.5	.034