


AVERY DENNISON MARKETING SPECIFICATION

HISTORY

THE SUBJECT MATTER DISCLOSED HEREIN EMBODIES PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF THE AVERY DENNISON CO. NONE OF WHICH SHALL BE COPIED, REPRODUCED, DISCLOSED TO OTHERS, PUBLISHED OR USED IN WHOLE OR IN PART, FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS BEING MADE AVAILABLE WITHOUT THE EXPRESS ADVANCE WRITTEN PERMISSION OF A DULY AUTHORIZED AGENT OF THE COMPANY. THIS DOCUMENT IS THE PROPERTY OF THE AVERY DENNISON CO. AND IS TO BE RETURNED TO THE COMPANY ON DEMAND.

REV.	DATE	DESCRIPTION
G	7.24.12	REMOVED THE WINDOWS IN THE FIR TREE
H	04.10.13	ITEM 8 FROM 6.20IN TO 6.14/6.22 AND ITEM 6 FROM .35IN TO .37



MOUNTING:	6.4MM TO 7.0MM HOLES	APPROVALS: ENG. APPR. <i>[Signature]</i> 4/15/13 Q.A. APPR. <i>[Signature]</i> 4/15/13	AVERY DENNISON <small>FASTENER DIVISION FITCHBURG, MA 01420 U.S.A. TEL. 1-800-225-5913 FAX. 978-353-8157</small>
TENSILE STRENGTH:	50 LBF / 22.7 KGF MIN.		
OPERATING TEMP RANGE:	-40°F (-40°C) TO 257°F (125°C)	SPECIFIED TOLERANCES ARE: .XX ± .03 IN. .X ± .7 MM .XXX ± .01 IN. .XX ± .25 MM ANGULAR: ± 2°	DESCRIPTION FIR TREE TIE - STANDARD
WEIGHT:	0.0700 OZ. / 2.06 GRAMS		
BUNDLE DIAMETER:	Ø 1.6MM / .063IN TO Ø 44.5MM / 1.75IN	MATERIAL IMPACT MODIFIED NYLON 6/6 HEAT STABILIZED	STOCK NO. 10709-0
TOOL:	12001 - HAND INSTALLATION TOOL 12500 - PNUM. INSTALLATION TOOL		
TOOL TENSION SETTING:	6 - 8	COLOR BLACK	REV. H
PACKAGING:	500/BAG, 10 BAGS/MASTER		

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[10709-0](#)