




# "Marshal Bean" Protective Rubber Covers with Tether Rope 780-555



*Fits Metal Shell  
M83513 Type  
Connectors*

### Rubber Covers for Tactical Equipment and Field Instruments

– These friction-fit covers provide dust and splash protection.

**Two Tether Styles** – Choose ring terminals for attachment to a panel, or choose slip knots for cable attachment.



**-55° to +125° Temperature Range**

### MATERIALS & FINISHES

Cover	SBR Rubber Per ASTM D2000 Type C
Cord	Nylon Per MIL-C-43307
Ring Terminal	Stainless Steel
Slip Collar	Kynar
Crimp Ring	Copper, Black Oxide Finish

### HOW TO ORDER 780-555 RUBBER PROTECTIVE COVERS

Series	Connector Layout	Nylon Cord Option	Nylon Cord Length	Attachment Option	Rubber Type
780-555	9P 9S	Omit – (leave blank) Cover only, no cord	Length in One Inch Increments  Example: "6" equals six inches.  ± .250 Inches ± 6.35 mm	Ring Terminal 06 – .125 (3.2) I.D.	Omit Standard Rubber
	15P 15S				
	21P 21S	05 – .167 (4.2) I.D.			
	25P 25S			04 – .197 (5.0) I.D.	
	31P 31S	SK – Slip Knot			
	37P 37S			C Conductive Rubber	
	51P 51S	51-2P 51-2S			
	67P 67S			69P 69S	
	69P 69S	100P 100S			
	100P 100S				
<b>Sample Part Number</b>					
780-555	37P	G	4	– SK	



Layout	A Max.		B Max.	
	In.	mm.	In.	mm.
9P, 9S	.830	21.08	.370	9.40
15P, 15S	.980	24.89	.370	9.40
21P, 21S	1.130	28.70	.370	9.40
25P, 25S	1.230	31.24	.370	9.40
31P, 31S	1.380	35.05	.370	9.40
37P, 37S	1.530	38.86	.370	9.40

Layout	A Max.		B Max.	
	In.	mm.	In.	mm.
51P, 51S	1.480	37.59	.410	10.41
51-2P, 51-2S	1.880	47.75	.370	9.40
67P, 67S	2.770	70.36	.370	9.40
69P, 69S	1.780	45.21	.410	10.41
100P, 100S	2.215	56.26	.460	11.68

Standard material contains trace amounts of sulfur (a vulcanizing agent) which is known to contribute to degradation/corrosion of silver plated components such as braid, etc. Specify MOD Code suffix -675 for sulfur-free material.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Glenair:

[780-555-51PG6-SK](#) [780-555-37PG4-SKC](#) [780-555-31PG6-SK](#) [780-555-25PG4-01](#) [780-555-25SG4-01](#) [780-555-15PG4-SKC](#) [780-555-37SG6-01](#) [780-555-25SG4-06](#) [780-555-9SG2-SKC](#) [780-555-21SG4-06](#) [780-555-9P-C](#) [780-555-15PG4-06](#) [780-555-21PG5-05](#) [780-555-69SG4-SK](#) [780-555-15PG6-06](#) [780-555-21SG7-05](#) [780-555-51SG4-05C](#)