



tesa® 60955 Anti-Slip Tape Conformable

Conformable Anti-Slip Tape for Irregular Surfaces

Product Information

Product Features

- Backing with good slip resistance and excellent conformability
- Perfectly conforms around edges, corners and adheres to irregular surfaces

*Slip resistance R13 according to DIN 51130

- Good chemical and weathering resistance
- Secure bonding to most surfaces
- Bright yellow and black-yellow colors ensure strong visibility for easy identification



tesa® 60955 is an anti-slip tape with a conformable backing and designed for adhering to tread plates and other irregular surfaces where good grip and safe footing is required. The conformable anti-slip tape is a single-sided tape, with a PET-liner, in form of a conformable, hand-tearable anti-slip backing with an acrylic adhesive. The backing consists of an aluminum carrier which is coated with mineral particles and has been specifically developed to conform around edges and adhere to irregular surfaces. The acrylic adhesive provides an excellent bond to most surfaces.

tesa® 60955 is certified according to DIN 51130 and available in the colors black, yellow and black-yellow. The bright yellow and black-yellow colored tapes have a strong visibility for easy identification in areas of safety concerns and for warning purposes, a perfect solution for complementing 5S manufacturing initiatives.

<span style="color: windowtext;

Application Fields

- tesa® 60955 is recommended for irregular surfaces where good grip and safe footing is required, e.g tread plates, fire escape ladders, loading ramps and platforms
- The conformable anti-slip tape can be used to cover flat surfaces with e.g. screw heads or rivets
- tesa® 60955 is a perfect solution for complementing 5S manufacturing initiatives

Product Construction

- | | | | |
|---------------------|---------|----------------------|------------------------------------------------|
| • Thickness of tape | 700 | • Thickness of liner | 50 |
| • Type of adhesive | acrylic | • Backing material | Aluminum carrier coated with mineral particles |
| • Total thickness | 750 µm | | |

Product Properties/Performance Values

- | | | | |
|-----------------------|---------|----------------------------|------------|
| • Elongation at break | 12 % | • Suitable for die cutting | yes |
| • Tensile strength | 60 N/cm | • Temperature resistance | -5 to +120 |

For latest information on this product please visit
<http://l.tesa.com/?ip=60955>



tesa[®] 60955

Anti-Slip Tape

Conformable

Adhesion to Values

Product Information steel 8 N/cm

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit
<http://l.tesa.com/?ip=60955>