

TR11-C, 1xPt100, 3-w, Cl.B, -50/250°C (F), terminal block, Not removable

TR11-C RTD assembly with fabricated threaded protection tube (tubing)

Item number: 45280444
Quantity: 1 pcs.
Order code: TR11-C-ZZZZ-13DR-BS1A-ZZ-AUGSGL9010005000165-ZZZZR12
ZZZZZZZZ-ZA-Z-WIKA0-ZZ
Overview: TR11-C, 1xPt100, 3-w, Cl.B, -50/250°C (F), terminal block, Not removable

Head / housing: BS (Alu), Strd.-gland, M20 x 1.5
Transmitter: Without (terminal block)

Protection tube: Straight, plain, with / w/o compression fitting
316L, Ø 6x1 mm, M24 x 1,5 - G1/2B comp., MH=50 mm (approx. 2 inch)
U1=100mm

Sealing: Without
Specifications according to data sheet: TE 60.03

Protection tube total length (spare) [L]: 165 mm

Thermowell specials: Without

Details: TR11-C RTD assembly with fabricated threaded protection tube (tubing)

Specifications according to data sheet: TE 60.03
1xPt100, 3-wire
Class B, IEC 60751
Temperature range of selected class: -50...+250°C
BS, Aluminum, flat cover
Cable entry: Standard cable entry
Thread size cable entry: M20 x 1.5
Transmitter: Without (terminal block)
Protection tube: Straight, plain, with / w/o compression fitting
Connection to neck tube: M24 x 1,5
Protection tube diameter: 6x1 mm
Protection tube material: Stainless steel 316L
Process connection: G 1/2 B compression fitting (metal ferrule)
Insertion length [A] [U1]: 100 mm
Neck length [MH/N]: 50 mm (approx. 2 inch)
Sealing: Without
Measuring insert: Not removable (no measuring insert)
Thermowell specials: Without