

ACCLIMATE"



IP68 SEALED ETHERNET SOCKET

Mates with:

SPECIFICATIONS

For complete specifications see www.samtec.com?RPBE

Insulator Material:

Black Liquid Crystal Polymer Contact:

Phosphor Bronze

Operating Temp Range:

-40 °C to +75 °C

Seal: Rubber

Screw:

Stainless Steel Nut:


Stainless Steel Sealing Washer:

Rubber

DUST CAPS

E	PORT	PART NO.	TYPE
ŀ	-01	DCA-RPBE-01-01-P	Push-On/ No Latch
Г	-01	DCA-RPBE-01-01-L	Latching
Ŀ	-02	DCA-RPBE-02-01-L	Latering

Note: Meets IP68 requirements for dust and waterproof sealing when mated or with dust cap.





PLATING

= 50 μ" (1.27 μm) Gold on contact,

Flash Gold on tail

RCE RPBE Audible click positive latching

Mates with:

SPECIFICATIONS

For complete specifications see www.samtec.com?RPCE

Insulator Material:

Glass Filled Thermoplastic

Contact:

Phosphor Bronze Shield:

Phosphor Bronze
Operating Temp Range:
-40 °C to +75 °C

Overmold: Rite Flex 640F


Seal: Rubber Screw: Stainless Steel Nut: Stainless Steel

Sealing Washer: Rubber Wire: 24 AWG

DUST CAPS

Ī	PORT	PART NO.	TYPE
Ī	-01	DCA-RPBE-01-01-P	Push-On/ No Latch
	-01	DCA-RPBE-01-01-L	Latching
	-02	DCA-RPBE-02-01-L	

Note: Meets IP68 requirements for dust and waterproof sealing when mated or with dust cap.



Some components removed for clarity

Due to technical progress, all designs, specifications and components are subject to change without notice. WWW.SAMTEC.COM