



| Model / Order-No. | TT-HVP 15B / 15010 |
|----------------------|-------------------------------------|
| Division Ratio | 1000:1 |
| Input Resistance | 100M Ω |
| Input Capacitor | 3,0pF \pm 0,5pF |
| Max. DC+AC peak | 20kV CAT 0 |
| Max. AC RMS. | 7kV CAT 0 |
| Max. DC | 10kV CAT 0 |
| Band Width | DC~40MHz (-3dB) |
| Rise Time | \leq 8,8ns |
| Signal / Noise | DC: > 60dB @ 1kHz ; > 50dB @ 1MHz |
| DCV Accuracy | \leq 6% |
| Temp. Coefficient | \leq 200 ppm/ $^{\circ}$ C |
| Compensation Range | 15pF ~ 30pF |
| Safety Standard | meets IEC61010-031:2015 |
| Measurement Category | CAT 0 / Pollution Degree 2 |
| Cable Length | 2m \pm 0.2m |
| Operation Temp. | -10 $^{\circ}$ C to 55 $^{\circ}$ C |
| Humidity | 85% RH or less (@ 35 $^{\circ}$ C) |
| Storage Temp. | -20 $^{\circ}$ C to 70 $^{\circ}$ C |
| Color: Handel / Body | Black / Yellow |
| Weight / Volume | 250g / 75(W) x 75(H) x 340(L) mm |

Fritz-Klatte-Str. 6,D - 65933 Frankfurt / E-Mail: info@testec.de
 Telefon: +49 (0) 69 - 94 333 5 – 0, Fax: +49 (0) 69 - 94 333 5 - 55