


Mini contactors

Mini contactors providing various connections and Accessories



Ratings

Frame size	AC3 ratings (IEC60947-4)				AC1 rating lth
	220 ~ 240V	380 ~ 440V	500 ~ 550V	690V	
6A	1.5kW	2.2kW	3kW	3kW	20A
	7A	6A	5A	4A	
9A	2.2kW	4kW	3.7kW	4kW	20A
	9A	9A	6A	5A	
12A	3kW	5.5kW	4kW	4kW	20A
	12A	12A	7A	5A	


Screw clamps



Fast-on



For conventional
screw connections




For fast-on
connections



Mini-overload relay



Overload relay
separately mounted




Reversing contactor


Cage clamps




Solder pins




Dimensions,mm




(Screw clamp type)




For screwless connections



To mount on printed circuit boards



Auxiliary contact units



Timer unit

Surge absorber unit

Quick selection table

Mini contactors & overloads

Mini contactors

3NO main contacts
1 auxiliary contacts



Screw clamp type



Fast-on type



Cage clamp type



Solder pin type

Frame size		6A		9A		12A	
Screw clamp type	AC coil	CGMS-6A		CGMS-9A		CGMS-12A	
	DC coil	CGMS-6D		CGMS-9D		CGMS-12D	
Fast-on type	AC coil	CGMF-6A		CGMF-9A		CGMF-12A	
	DC coil	CGMF-6D		CGMF-9D		CGMF-12D	
Cage clamp type	AC coil	CGMC-6A		CGMC-9A		CGMC-12A	
	DC coil	CGMC-6D		CGMC-9D		CGMC-12D	
Solder pin type	AC coil	CGMP-6A		CGMP-9A		CGMP-12A	
	DC coil	CGMP-6D		CGMP-9D		CGMP-12D	

Ratings / IEC60947-4		kW		A		kW		A	
AC1			20		20				20
AC3	200/240V	1.5	7	2.2	9	3	12		
	380/440V	2.2	6	4	9	5.5	12		
	690V	3	4	4	5	4	5		

Ratings / UL508		hp		A		hp		A	
continuous current		lth = 20A (maximum for cage clamp type is 10A)							
single phase	115V	0.5		0.5		1*			
	230V	1		1.5		2**			
three phase	200V	*		*		*			
	230V	1.5		3		3			
	460V	3		5		7.5***			
	575V	3		5		7.5			
NEMA size		00		00		00			

Additional auxiliary contacts	Screw clamp type	Fast-on type	Cage clamp type	Solder pin type
2-pole, Front mount	AX-2M	AX-2MF	AX-2MC	AX-1MP
4-pole, Front mount	AX-4M	AX-4MF	AX-4MC	
2-pole, Side mount	AX-1M	AX-1MF	AX-1MC	

See page 30 for more details

Overload Relays

<p>Bimetallic style</p> <p>Type CGT</p> <p>Class 10A</p>	<p>CGT-12M</p>	<p>Setting ranges (A)</p> <table border="0"> <tr> <td>0.1 - 0.16</td> <td>4 - 6</td> </tr> <tr> <td>0.16 - 0.25</td> <td>5 - 8</td> </tr> <tr> <td>0.25 - 0.4</td> <td>6 - 9</td> </tr> <tr> <td>0.4 - 0.63</td> <td>7 - 10</td> </tr> <tr> <td>0.63 - 1</td> <td>9 - 13</td> </tr> <tr> <td>1 - 1.6</td> <td>12 - 16</td> </tr> <tr> <td>1.6 - 2.5</td> <td></td> </tr> <tr> <td>2.5 - 4</td> <td></td> </tr> </table>	0.1 - 0.16	4 - 6	0.16 - 0.25	5 - 8	0.25 - 0.4	6 - 9	0.4 - 0.63	7 - 10	0.63 - 1	9 - 13	1 - 1.6	12 - 16	1.6 - 2.5		2.5 - 4		<p>Base for separate mount</p>	<p>See page 27 for more details</p>
0.1 - 0.16	4 - 6																			
0.16 - 0.25	5 - 8																			
0.25 - 0.4	6 - 9																			
0.4 - 0.63	7 - 10																			
0.63 - 1	9 - 13																			
1 - 1.6	12 - 16																			
1.6 - 2.5																				
2.5 - 4																				
Differential		CGT-12M																		
Non-differential (3-heater)		CGTH-12M/3																		
Non-differential (2-heater)		CGTH-12M																		

Note: * = 1/2 for cage clamp type, ** = 1.5hp for cage clamp type, *** = 5hp for cage clamp type

Contactors

- For motor control
- 3 main plus 1 auxiliary contacts
- Coil voltage : A.C.



Cage clamp connection types

Frame size	AC3 ratings (IEC60947-4)				AC1 rating Ith	Auxiliary contact (standard)	Type
	220 ~ 240V	380 ~ 440V	500 ~ 550V	690V			
6A	1.5kW 7A	2.2kW 6A	3kW 5A	3kW 4A	20A	1NO or 1NC	CGMC-6A
9A	2.2kW 9A	4kW 9A	3.7kW 6A	4kW 5A	20A	1NO or 1NC	CGMC-9A
12A	3kW 12A	5.5kW 12A	4kW 7A	4kW 5A	20A	1NO or 1NC	CGMC-12A



Solder pin connection types

Frame size	AC3 ratings (IEC60947-4)				AC1 rating Ith	Auxiliary contact (standard)	Type
	220 ~ 240V	380 ~ 440V	500 ~ 550V	690V			
6A	1.5kW 7A	2.2kW 6A	3kW 5A	3kW 4A	20A	1NO or 1NC	CGMP-6A
9A	2.2kW 9A	4kW 9A	3.7kW 6A	4kW 5A	20A	1NO or 1NC	CGMP-9A
12A	3kW 12A	5.5kW 12A	4kW 7A	4kW 5A	20A	1NO or 1NC	CGMP-12A

Coil voltage, AC 50/60Hz

24, 36, 42, 48, 110, 115, 120, 127, 200 / 208, 220, 220 / 230, 230 / 240, 256, 277, 380 / 400
400, 440, 480, 500, 550V AC

Ordering information

Type, Auxiliary contact and Coil voltage

For more information

- Drawings → page 34
- Reversing contactors → page 23
- Overload relays → page 27
- Optional accessories → page 29~33

Certificate
CE, ULcUL

Contactors

- For motor control
- 3 main plus 1 auxiliary contacts
- Coil voltage : D.C.



Cage clamp connection types

Frame size	AC3 ratings (IEC60947-4)				AC1 rating Ith	Auxiliary contact (standard)	Type
	220 ~ 240V	380 ~ 440V	500 ~ 550V	690V			
6A	1.5kW 7A	2.2kW 6A	3kW 5A	3kW 4A	20A	1NO or 1NC	CGMC-6D
9A	2.2kW 9A	4kW 9A	3.7kW 6A	4kW 5A	20A	1NO or 1NC	CGMC-9D
12A	3kW 12A	5.5kW 12A	4kW 7A	4kW 5A	20A	1NO or 1NC	CGMC-12D



Solder pin connection types

Frame size	AC3 ratings (IEC60947-4)				AC1 rating Ith	Auxiliary contact (standard)	Type
	220 ~ 240V	380 ~ 440V	500 ~ 550V	690V			
6A	1.5kW 7A	2.2kW 6A	3kW 5A	3kW 4A	20A	1NO or 1NC	CGMP-6D
9A	2.2kW 9A	4kW 9A	3.7kW 6A	4kW 5A	20A	1NO or 1NC	CGMP-9D
12A	3kW 12A	5.5kW 12A	4kW 7A	4kW 5A	20A	1NO or 1NC	CGMP-12D

Coil voltage, DC

- ① Standard type : 12, 20, 24, 36, 42, 48, 60, 72, 110, 120, 125, 220, 240, 250V DC
- ② Low consumption type : 12, 20, 24, 48, 72, 110, 120V DC(Low)
- ③ Wide Voltage : 12, 20, 24, 48, 72, 110, 12V DC(Wide)

Ordering information

Type, Auxiliary contact and Coil voltage

For more information


- Drawings → page 34
- Reversing contactors → page 25
- Overload relays → page 27
- Optional accessories → page 29~33

Certificate
CE, ULcUL

Mini contactors


Dimensions

CGMS-12A




0.17kg

CGMS-12D




0.23kg

CGMUS-12A



0.36kg

CGMUS-12D



0.48kg


Mini contactors

Characteristic

Electrical lifespan of contactors

Use in category AC-3


($U_e \geq 440V$)



(1) The dotted lines are only applicable to CGMS-12A contactors.

Use in category AC-4

($U_e \geq 440V$)



(1) The dotted lines are only applicable to CGMS-12A contactors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Carlo Gavazzi:

[CGMC-6A-120-10](#) [CGMC-6D-24S-10](#) [CGMS-12D-24L-10](#) [CGMS-9A-208-10](#) [CGMS-9A-220-10](#) [CGMU-9A-120-20](#)
[CGMU-9A-240-20](#) [CGMP-9D-24S-10](#) [CGMS-12A-240-10](#) [CGMS-12A-480-01](#) [CGMU-12A-24-02](#) [CGMU-12A-24-11](#)
[CGMU-12A-24-20](#) [CGPMDL483075B1AN311](#) [CGMC-6D-24S-01](#) [CGMS-12A-230-10BP](#) [CGMS-12A-24-01](#) [CGMU-](#)
[12D-24-02](#) [CGMU-6D-24-20](#) [CGMU-9A-120-11](#) [CGMU-9D-24-11](#) [CGMP-9D-24S-01](#) [CGMS-12A-24-10](#) [CGMU-12D-](#)
[12-20](#) [CGMC-6A-120-01](#) [CGMC-9A-240-10](#) [CGMS-12A-208-01](#) [CGMC-6A-240-10](#) [CGMS-6D-24S-01](#) [CGMS-9A-24-](#)
[10](#) [CGMS-9D-12S-10](#) [CGMU-6A-120-11](#) [CGMU-6A-24-20](#) [CGMP-6D-24S-10](#) [CGD60-TE110V](#) [CGMP-12D-24S-10](#)
[CGMS-6A-240-01](#) [CGMS-6A-240-10](#) [CGMS-9A-240-01](#) [CGMS-9A-240-10](#) [CGMU-12D-24-20](#) [CGMS-12A-230-10](#)
[CGMU-6A-120-02](#) [CGMS-6A-120-01](#) [CGMF-9D-24S-10](#) [CGMS-12A-208-10](#) [CGMS-6A-120-10](#) [CGMS-6A-24-10](#)
[CGMU-9A-120-02](#) [CGMS-6D-24S-10](#) [CGMS-9A-230-10](#) [CGMS-9A-24-01](#) [CGMU-6D-24-11](#) [CGMU-9D-24-20](#)
[CGMC-12A-24-10](#) [CGMS-12A-230-01](#) [CGMS-12A-230-01BP](#) [CGMS-6A-208-10](#) [CGMC-9A-24-10](#) [CGMP-6D-24S-01](#)
[CGMS-12A-240-01](#) [CGMS-6A-230-01](#) [CGMS-6A-230-10](#) [CGMU-6A-120-20](#) [CGMU-6D-24-02](#) [CGMS-12A-220-01](#)
[CGMS-12A-220-10](#) [CGMU-9A-24-20](#) [CGMU-9D-24-02](#) [CGMC-12A-208-10](#) [CGMC-9D-24S-01](#) [CGMP-12D-24S-01](#)
[CGMS-6A-208-01](#) [CGMC-12A-120-01](#) [CGMC-12A-120-10](#) [CGMC-12A-240-10](#) [CGMC-12D-24S-01](#) [CGMC-12D-24S-](#)
[10](#) [CGMC-9A-120-01](#) [CGMS-9A-120-10](#) [CGMS-9D-24L-01](#) [CGMS-9D-24L-10](#) [CGMS-9D-24S-01](#) [CGMS-9D-24S-10](#)
[CGMP-9A-120-10](#) [CGMS-12A-120-01](#) [CGMS-12A-120-10](#) [CGMS-12D-24S-01](#) [CGMS-12D-24S-10](#) [CGMS-9A-120-](#)
[01](#) [CGMC-9A-120-10](#) [CGMP-12A-120-01](#) [CGMP-12A-120-10](#) [CGMP-6A-120-01](#) [CGMP-6A-120-10](#) [CGMP-9A-120-](#)
[01](#) [CGD60TE110V](#) [CGMU-12A-120-20](#)