



ENGLISH

**Datasheet**

**Stock No: 124-6646**

# **RS PRO 2 WAY IN-LINE CABLE SOCKET 10A IP68**



## **Specifications:**

From RS PRO, these threaded sockets are serious contenders for your application. This particular model has a bigger and stronger shell. That coupled with the IP68 rating excels in harsh environments. When choosing a female connector, this version should really be one you consider.

|                            |  |
|----------------------------|--|
| Material                   | Plastic  |
| IP Rating                  | IP68   |
| Coupling Type              | Threaded coupling                              |
| Shell                      | Nylon66, fire resistance:V-0                   |
| Insert material            | PPS max temperature 260°C, fire resistance:V-0 |
| Contact material           | Brass with gold plating                        |
| Termination                | Solder/Crimp                                   |
| Cable outer diameter range | 6-10mm   |
| Mating cycle               | > 500  |
| Temperature range          | -25°C~+85°C                                    |
| Insulation resistance MΩ   | 2000   |

