

Datasheet

Stock No: 124-6653

ENGLISH

RS Pro 3 WAY FRONT MOUNT SOCKET 10A IP68



Specifications:

From RS Pro, these threaded sockets are serious contenders for your application. This particular model has a bigger and stronger shell. That coupled with the IP68 rating excels in harsh environments. When choosing a female connector, this version should really be one you consider.



ENGLISH

Material	Plastic
IP Rating	IP68
Coupling Type	Threaded coupling
Shell	Nylon66,fire resistance:V-0
Insert material	PPS max temperature 260℃, fire resistance:V-0
Contact material	Brass with gold plating
Termination	Solder/Crimp
Cable outer diameter range	6-10mm
Mating cycle	> 500
Temperature range	-25℃~+85℃
Insulation resistance $M\Omega$	2000