



ENGLISH

Datasheet

# RS Pro 2, 3 & 5 IN-LINE CABLE SOCKET 25A IP68



## Specifications:

From RS Pro, these threaded sockets are serious contenders for your application. This particular model has a bigger and stronger shell complimented by its cable to cable (inline) connection. That coupled with the IP68 rating, makes sure that this industrial connector excels in harsh environments. When choosing a female connector, this version should really be one you consider.



ENGLISH

Coupling Type	Threaded Coupling
IP Rating	IP68
Material	Plastic
Shell	Nylon66, fire resistance:V-0
Insert Material	PPS max temperature 260°C, fire resistance:V-0
Contact Material	Brass with gold plating
Termination	Solder/Screw/Crimp
Cable outer diameter range	I : 4.5-7mm II : 7-12mm
Mating cycle	>500
Temperature range	-25°C~+85°C
Insulation resistance MΩ	2000