

Datasheet


ENGLISH

RS PRO 2, 3 & 5 WAY CABLE SOCKET 25A IP68

Stock No:

124-6683,124-6684,124-6685,124-6686,124-6687,124-6688





Specifications:

From RS PRO, these threaded sockets are serious contenders for your application. This particular model has a bigger and stronger shell. That coupled with the IP68 rating, makes sure that this industrial connector excels in harsh environments. When choosing a female connector, this version should really be one you consider.

Coupling Type	Threaded Coupling
IP Rating	IP68
Material	Plastic
Shell	Nylon66, fire resistance: V-0
Insert Material	PPS max temperature 260°C, fire resistance: V-0
Contact Material	Brass with gold plating
Termination	Solder/Screw/Crimp
Cable out diameter range	7-12mm
Mating cycle	>500
Temperature range	-25°C~+85°C
Insulation resistance MΩ	2000