

Datasheet Stock No: 1246690

## ENGLISH

## RS PRO Cable Mount Connector



## Specifications:

From RS Pro, these threaded plugs are serious contenders for your application. This particular model has a bigger and stronger shell. That coupled with the IP68 rating excels in harsh environments. When choosing a male connector, this version should really be one you consider.



## ENGLISH

Material	Plastic
IP Rating	IP68
Coupling Type	Threaded coupling
Shell	Nylon66, fire resistance: V-0
Insert material	PPS max temperature 260°C, fire resistance:V-0
Contact material	Brass with gold plating
Termination	Solder/Crimp
Cable outer diameter range	6-10mm
Mating cycle	> 500
Temperature range	-25°C~+85°C
Insulation resistance $M\Omega$	2000