

RS Pro 2, 3, 4 & 5 WAY M12 CABLE MOUNT PUSH-PULL CABLE PLUGS



Specifications:

From RS Pro, these push-pull plugs are serious contenders for your application. The convenient push-pull connection, makes it perfect in situations where accidental disconnects occur. That coupled with the IP67 rating, makes sure that this industrial connector excels in harsh environments. When choosing a male connector, this version should really be one you consider.

Coupling Type	Push and Pull
IP Rating	IP67
Material	Metal
Shell	Brass with chrome plating
Insert Material	PPS max temperature 260°C, fire resistance: V-0
Contact Material	Brass with gold plating
Termination	Solder
Cable out diameter range	II: 5-8mm
Mating cycle	>500
Temperature range	-40°C~+85°C
Insulation resistance MΩ	2000