

Search within category **GO**

**BUY NOW**

**DESIGN / INSTALL**

**PRT2S-M0**

Pan-Ty® releasable tie, standard cross section, 7.4 (188mm) length, weather resistant nylon 6.6, black, bulk package.

**Specs** **Packaging Details** **Documents** [★ Add to Favorites](#) [Add to BOM](#)

Material	Weather Resistant Nylon 6.6
Overall Length (In.)	7.4
Overall Length (mm)	188
Color	Black
Overall Width (In.)	0.19
Overall Width (mm)	4.8
Minimum Loop Tensile Strength (N)	222
Minimum Loop Tensile Strength (lb)	50
Maximum Installation Temperature (°F)	32
Resistance Properties	UV Resistant
Standards Met	Rated for AH-2 Plenum
Application	General
Cross Section	Standard
Length (In.)	7.40
Length (mm)	188.0
Locking Style	Releasable
UV Resistant	Yes
Tool	Hand install only
Thickness In (mm)	0.05 (1.3)
CE Compliant	Yes
CSA Certified	Yes
Continuous Use Temperature Range	-76°F (-60°C) - 185°F (85°C)
Operating Temperature	-76°F (-60°C) - 185°F (85°C)
Part Features	Release tab permits easy release and re-use where changes are anticipated.
UL 62275 Compliant (Type 1, 11)	No
UL 62275 Compliant (Type 2S, 21S)	Yes
UL Listed (File #E56854)	Yes
UL Recognized (File #E56854)	No
RoHS Compliancy Status	Compliant

