



Search within category GO



HST0.4-6-XY

Thick wall adhesive lined, .4" (10.2mm) diameter, 6.0" (152.4mm) length, adhesive lined black cross-linked polyolefin, 10 pc. package quantity.

HST0.4-6-XY replaces HST0.4-6-X

BUY NOW

DESIGN / INSTALL

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Note	HST0.4-6-XY replaces HST0.4-6-X			
Material	Highly Flame Retardant Adhesive Lined Cross-Linked Polyolefin			
Color	Black			
Flammability Rating	VW-1			
Shrink Ratio	3:1			
Temperature Range	-67°F - 230°F (-55°C - 110°C)			
Length (In.)	6.00			
Length (mm)	152.4			
Max. Recovered I.D. (In.)	0.160			
Max. Recovered I.D. (mm)	4.1			
Min. Expanded I.D. (In.)	0.400			
Min. Expanded I.D. (mm)	10.2			
Nominal Recovered Wall Thickness (In.)	0.08			
Nominal Recovered Wall Thickness (mm)	2.0			
Copper Conductor Size Range	#12 AWG - #6 AWG			
CSA Certified	Yes			
Military Specification	AMS-DTL-23053/15 Class 1 (material performance only)			
UL Listed	Yes			
UL Recognized	Yes			
Length (m)	0.1524			
Sub Brand	Wet-Shrink			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	10			