

**ARCA 302015W**



Sample photo

**Order symbol:** ARCA 302015W  
**Product nbr:** 8120122  
**Description:** Cabinet, PC  
**Remarks:** Cover with window, 1-point locking

**EAN:** 6418074079916  
**EI. number:**  
 Finland: 3423190  
 Electric No. 8212091786  
 Denmark:  
 Electric No. Sweden: 2500138

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
<b>mm:</b>	300	200	150	MPP ARCA 3020	Mounting plate perforated (250x150x2 mm - 26x11 mm)
<b>inch:</b>	11.8	7.9	5.9	MPMP ARCA 3020	Mounting plate multiperforated (250x150x2 mm - □3.6 mm)
Materials:				MPX ARCA 3020	Mounting plate (250x150 mm)
<b>Material:</b>	Polycarbonate			DRS ARCA 302015	DIN rail frame set
<b>Base colour:</b>	RAL 7035 -light grey			DRS ARCA 302021	DIN rail frame set
<b>Cover colour:</b>	RAL 7035 -light grey			IDS ARCA 3020	Inner door set
<b>Gasket material:</b>	Polyurethane			PMK ARCA 20	Pole mounting kit
Temperatures:				RCS ARCA 3020	Rain canopy set
<b>Temperature °C (short term):</b>	-40 ... 120 °C			SBK ARCA 20	Support bar kit
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			SBK ARCA 30	Support bar kit
<b>Temperature °F (short term):</b>	-40 ... 250 °F			Rating:	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			Ingress Protection (EN 60529): IP65	
Accessories:				Impact Resistance (EN 62262): IK08	
MPS ARCA 3020	Mounting plate (250x150x2 mm)			Electrical insulation: Totally insulated	
				Halogen free (DIN/VDE 0472, Part 815): 1	
				UV resistance: UL 508	
				Flammability Rating: UL 94 5VA	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 4, 4X, 12 and 13	
				Certificates:	
				SGS Fimko	

