



| REVISIONS | | | |
|-----------|------------------|------|----------|
| Rév. | Description | Visa | Date |
| A | Drawing creation | EL | 30.12.21 |
| | | | |
| | | | |

Kit size: 86,0 x 210,0
[3.39" x 8.27"]



Recto

Verso




-  x 60 - Black
-  x 60 - Black
-  x 60 - Black
-  x 60 - Blue
-  x 60 - Yellow + Green








TOTAL : 300 labels

50 labels/sheet

6 sheets/kit

TE PN: 2404100-1




-  Kiss cut
-  Die cut
-  Back slit
-  Adhesive cut
-  Perforation
-  45° die cut
-  2 kiss cut enductions

All dimensions in mm/[inch]
Labels are centered on the liner except against indication

| | |
|-------------------------------|---------------|
| Overlamination: / | |
| Material : | White PVC |
| Adhesive : | Permanent |
| Liner: | Kraft |
| DWN EL / 30.12.21 | DATE |
| CHK EL / 30.12.21 | DATE |
| APVD XX / xx.xx.xx | DATE |
| PRODUCT SPEC TTDS-280 | DATE |
| APPLICATION SPEC | DATE |
| WEIGHT 4,2 g (label) | SIZE |
| SCALE NTS | CAGE CODE |
| TE Connectivity | |
| Part | |
| 3PHASES-LABEL-BK-300 | |
| TE DRAWING | RESTRICTED TO |
| A4 | FB1U7 |
| 3PHASES-LABEL-BK-300_20211230 | |
| CUSTOMER DRAWING | SHEET 1 OF 1 |
| | REV A |

Customer drawing

| TOLERANCES | |
|---------------------|--------|
| Label height : | ±0,2 |
| Label width : | ±0,2 |
| Web width : | ±0,5 |
| Vertical repeat : | ±0,3* |
| Horizontal repeat : | ±0,5* |
| Print positioning : | ±0,5* |
| Left margin : | ±0,5 |
| Quantity : | 0% +2% |
| * non accumulating | |

| | |
|---|---|
| THIS DRAWING IS A CONTROLLED DOCUMENT | |
| DIMENSIONS | TOLERANCES UNLESS OTHERWISE SPECIFIED |
|  | 0/PLC 1/PLC 2/PLC 3/PLC 4/PLC ANGLES |
| MATERIAL | FINISH |
| SEE TABLE | Gloss |