# **KSA & KSL MKII Series High Performance Sealed Tact Switch**

#### Features/Benefits

- Highest tact switch sealing performance
- Improved sealing through a modification of the crimping technique and to a double overmolding of the terminal
- Totally sealed
- Up to 1M operations
- RoHS compliant and compatible

### Typical Applications

- Automotive
- Industrial
- Telecommunication networks
- Household appliances
- Heating control systems



#### **Specification**

CONTACT ARRANGEMENT: SPST, N.O.

TERMINALS: PC pins SEALING: IP65

Double overmold on terminals

#### Mechanical

	Actuation force	Operating life	Travel to
Туре	N (grams)	(operations)	make
KSA0M212	$1,3 \pm 0,3$	100,000	$0.5 \pm 0.15$
KSA0M312	$1,3 \pm 0,3$	1,000,000	$0.5 \pm 0.15$
KSA0M412	$3,25 \pm 0,5$	100,000	$0.6 \pm 0.25$
KSA0M512	5 ± 1,25	100,000	$0.7 \pm 0.25$

#### **Packaging**

Delivered in boxes of 500 pieces (250 pieces for KSL)

NOTE: Specifications listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

Other versions in terms of force, termination length and corrosion protection available. Please contact your sales representative.

This data sheet does not provide enough information for applications which require a certain level of quality or safety such as automotive, medical systems, safety equipment, Please contact your sales representative to get contractual specification package.

Electrical	Silver	Gold		
MAXIMUM POWER:	1 VA	0.2 VA		
MAXIMUM VOLTAGE:	32 VDC	32 VDC		
MINIMUM VOLTAGE:	20 mV	20 mV		
MAXIMUM CURRENT:	50 mA	10 mA		
MINIMUM CURRENT:	1 mA	1 mA		
DIEL COTDIO OTDENOTILES OF O Vision -				

DIELECTRIC STRENGTH: ≥ 250 Vrms CONTACT RESISTANCE:  $\leq$  100m  $\Omega$ INSULATION RESISTANCE (100 V): ≥ 109 Ω

BOUNCE TIME: ≤ 1 ms

**Environmental** Silver Gold **OPERATING TEMPERATURE:** -40°C to 85°C -40°C to 125°C STORAGE TEMPERATURE: -40°C to 85°C -55°C to 125°C

#### **Process**

Wave soldering compatible with lead free soldering profile.


#### **Packaging**

Can be delivered in tubes of 65 pieces for automatic insertion or in boxes of 500 pieces for manual insertion.

#### **How To Order**

Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and place it in the appropriate box.

However, please note that all the combinations of these options are not feasible. For any part number different from those listed above, please consult your local represenative.






# **KSA & KSL MKII Series High Performance Sealed Tact Switch**


## TYPE ----


#### **KSA & KSL**


MANUAL INSERTION















### **KSA & KSL**


#### AUTOMATIC INSERTION











Dimensions are shown: mm (inches) Specifications and dimensions subject to change

