



coding style table

	style A: for connectors 6-pole
	style B: for connectors from 10 to 14-pole
	style C: for connectors from 16 to 64-pole

further information see: DS 09182100600

	All rights reserved Department EC PD - DE	Created by STORCK	Inspected by LEHNERT	Standardisation HOFFMANN	Date 2016-04-05	State Final Release	Ref. Sub.
	HARTING Electronics GmbH D-32339 Espelkamp	Title SEK 18 female conn with open end cover strain relief			Doc-Key / ECM-Nr. 100662934/UGD/007/A 50000099698		Rev. A
		Type TB	Number 09185XXX813		Page 1/2		

		performance level			dimensions								
		PL3	PL2	S4	insulator colour	remark	quantity	A max.	B	C	D		
no. of contacts	part number	part number	part number										
06	09 18 506 7813	09 18 506 6813	09 18 506 5813	grey	-		12,2	2 x 2,54 (=5,08)	2	8,02			
10	09 18 510 7813	09 18 510 6813	09 18 510 5813				17,3	4 x 2,54 (=10,16)	3,8	13,1			
14	09 18 514 7813	09 18 514 6813	09 18 514 5813				22,4	6 x 2,54 (=15,24)	3,8	18,18			
16	09 18 516 7813	09 18 516 6813	09 18 516 5813				24,9	7 x 2,54 (=17,78)	3,8	20,72			
20	09 18 520 7813	09 18 520 6813	09 18 520 5813				30	9 x 2,54 (=22,86)	3,8	25,8			
26	09 18 526 7813	09 18 526 6813	09 18 526 5813				37,6	12 x 2,54 (=30,48)	3,8	33,42			
30	09 18 530 7813	09 18 530 6813	09 18 530 5813				42,7	14 x 2,54 (=35,56)	3,8	38,56			
34	09 18 534 7813	09 18 534 6813	09 18 534 5813				47,8	16 x 2,54 (=40,64)	3,8	43,58			
40	09 18 540 7813	09 18 540 6813	09 18 540 5813				55,4	19 x 2,54 (=48,26)	3,8	51,2			
50	09 18 550 7813	09 18 550 6813	09 18 550 5813				68,1	24 x 2,54 (=60,96)	3,8	63,9			
60	09 18 560 7813	09 18 560 6813	09 18 560 5813				80,8	29 x 2,54 (=73,66)	3,8	76,6			
64	09 18 564 7813	09 18 564 6813	09 18 564 5813				85,9	31 x 2,54 (=78,74)	3,8	81,68			
06	09 18 506 7813 001	09 18 506 6813 001	09 18 506 5813 001				black	-		12,2	2 x 2,54 (=5,08)	2	8,02
10	09 18 510 7813 001	09 18 510 6813 001	09 18 510 5813 001							17,3	4 x 2,54 (=10,16)	3,8	13,1
14	09 18 514 7813 001	09 18 514 6813 001	09 18 514 5813 001	22,4	6 x 2,54 (=15,24)	3,8				18,18			
16	09 18 516 7813 001	09 18 516 6813 001	09 18 516 5813 001	24,9	7 x 2,54 (=17,78)	3,8				20,72			
20	09 18 520 7813 001	09 18 520 6813 001	09 18 520 5813 001	30	9 x 2,54 (=22,86)	3,8				25,8			
26	09 18 526 7813 001	09 18 526 6813 001	09 18 526 5813 001	37,6	12 x 2,54 (=30,48)	3,8				33,42			
30	09 18 530 7813 001	09 18 530 6813 001	09 18 530 5813 001	42,7	14 x 2,54 (=35,56)	3,8				38,56			
34	09 18 534 7813 001	09 18 534 6813 001	09 18 534 5813 001	47,8	16 x 2,54 (=40,64)	3,8				43,58			
40	09 18 540 7813 001	09 18 540 6813 001	09 18 540 5813 001	55,4	19 x 2,54 (=48,26)	3,8				51,2			
50	09 18 550 7813 001	09 18 550 6813 001	09 18 550 5813 001	68,1	24 x 2,54 (=60,96)	3,8				63,9			
60	09 18 560 7813 001	09 18 560 6813 001	09 18 560 5813 001	80,8	29 x 2,54 (=73,66)	3,8				76,6			
64	09 18 564 7813 001	09 18 564 6813 001	09 18 564 5813 001	85,9	31 x 2,54 (=78,74)	3,8				81,68			
06	09 18 506 7813 58U	09 18 506 6813 58U	09 18 506 5813 58U	grey	bulk packaging	3000 pieces				12,2	2 x 2,54 (=5,08)	2	8,02
10	09 18 510 7813 58U	09 18 510 6813 58U	09 18 510 5813 58U			3000 pieces				17,3	4 x 2,54 (=10,16)	3,8	13,1
14	09 18 514 7813 58U	09 18 514 6813 58U	09 18 514 5813 58U			2500 pieces	22,4	6 x 2,54 (=15,24)	3,8	18,18			
16	09 18 516 7813 58U	09 18 516 6813 58U	09 18 516 5813 58U			2500 pieces	24,9	7 x 2,54 (=17,78)	3,8	20,72			
20	09 18 520 7813 58U	09 18 520 6813 58U	09 18 520 5813 58U			2000 pieces	30	9 x 2,54 (=22,86)	3,8	25,8			
26	09 18 526 7813 58U	09 18 526 6813 58U	09 18 526 5813 58U			1500 pieces	37,6	12 x 2,54 (=30,48)	3,8	33,42			
30	09 18 530 7813 58U	09 18 530 6813 58U	09 18 530 5813 58U			2000 pieces	42,7	14 x 2,54 (=35,56)	3,8	38,56			
34	09 18 534 7813 58U	09 18 534 6813 58U	09 18 534 5813 58U			1000 pieces	47,8	16 x 2,54 (=40,64)	3,8	43,58			
40	09 18 540 7813 58U	09 18 540 6813 58U	09 18 540 5813 58U			1000 pieces	55,4	19 x 2,54 (=48,26)	3,8	51,2			

	All rights reserved	Created by	Inspected by	Standardisation	Date	State	
	Department EC PD - DE	STORCK	LEHNERT	HOFFMANN	2016-04-05	Final Release	
HARTING Electronics GmbH D-32339 Espelkamp		Title SEK 18 female conn with open end cover strain relief				Doc-Key / ECM-Nr. 100662934/UGD/007/A 50000099698	
		Type	Number		Rev.	Page	
		TB	09185XXX813		A	2/2	