



Product data sheet

Power tools for trade & industry

Detector

GMS 120



Simple and intuitive – the logical favourite for locating objects effectively

The most important data

Max. detection depth	120 mm
Bosch Radar Technology	no
Detectable objects	magnetic metals (e.g. iron), ...

Part Number 0 601 081 000

[> More product information](#)

Technical data

Technical data

Bosch Radar Technology	no
Detectable objects	magnetic metals (e.g. iron), non-magnetic metals (e.g. copper), live cables, wooden substructures
Max. detection depth	120 mm
Detection depth, magnetic metal, max.	120 mm
Detection depth, non-magnetic metal, max.	80 mm
Detection depth, live cables, max.	50 mm
Detection depth, wooden substructures, max.	38 mm
Wall types	Drywall, Universal
Dust and splash protection	IP 54
Material identification	Live cable, Metal
Power supply	1 x 9 V 6LR61
Automatic deactivation, approx.	5 minutes
Weight, approx.	0.27 kg



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Automatic calibration avoids application errors for more reliable and confident work
- Locate metal and live wire in various wall types as well as wooden substructures in drywall
- Detects objects in walls before drilling for increased safety, ideal for renovation work

