

# IGBT ТРАНЗИСТОРЫ

Наименование	Uкз,В	Iк,А	Рк,Вт	S,мА/В	Корпус	Тип
HGTD3N60B3S	600	3,0			TO-220AB	
HGTG12N60B3	600	12,0			TO-220AB	
HGTG12N60B3D	600	12,0			TO-220AB	
HGTG12N60C3D	600	12,0			TO-220AB	
HGTG30N60B3	600	30,0			TO-220AB	
HGTP12N60B3	600	12,0			TO-220AB	
HGTP12N60B3D	600	12,0			TO-220AB	
HGTP14N36G3VL	360	14,0			TO-220AB	
HGTP14N40F3VL	400	14,0			TO-220AB	
HGTP20N60B3	600	20,0			TO-220AB	
HGTP3N60B3	600	3,0			TO-220AB	
HGTP7N60B3	600	7,0			TO-220AB	
HGTP7N60B3D	600	7,0			TO-220AB	
IRG4BC20UD	600	13,0	60	1400	TO-220AB	N-канал
IRG4BC30F	600	31,0	100	6100	TO-220AB	N-канал
IRG4BC30U	600	23,0	100	3100	TO-220AB	N-канал
IRG4BC30UD	600	23,0	100	3100	TO-220AB	N-канал
IRG4BC30W	600	12,0			TO-220	N-канал
IRG4PC30F	600	17,0			TO-247AC	N-канал
IRG4PC30KD						N-канал
IRG4PC30UD	600	23,0	100	3100	TO-247AC	N-канал
IRG4PC30W	600	23,0	100	1600	TO-247AC	N-канал
IRG4PC40KD						
IRG4PC40U	600	40,0	160	11000	TO-247AC	N-канал
IRG4PC50KD	600	52,0	104	17000	TO-247AC	N-канал
IRG4PC50S	600	40			TO-247AC	N-канал
IRG4PC50U	600	55,0	200	16000	TO-247AC	N-канал
IRG4PC50UD	600	55,0	200	16000	TO-247AC	N-канал
IRG4PC50W	600	55,0	200	27000	TO-247AC	N-канал

Наименование	Uкз,В	Iк,А	Рк,Вт	S,мА/В	Корпус	Тип
IRG4PF50W						
IRG4PF50WD						
IRG4PH30K						
IRG4PH40KD						
IRG4PH40U	*					
IRG4PH40UD						
IRG4PH50K	1200	45,0	200	13000	TO-247AC	N-канал
IRG4PH50KD	1200	45,0	200	13000	TO-247AC	N-канал
IRG4PSC71UD						
IRG4ZC70UD						
IRGBC20FD2	600	16,0			TO-220	N-канал
IRGBC30F	600	16,0			TO-220	N-канал
IRGBC30MD2	600	16,0			TO-220	N-канал
IRGBC30MD2-S	600	16,0	100	3300	SMD-220	N-канал
IRGP440U	500	40,0	160	6600	TO-247AC	N-канал
IRGP450UD2	500	33,0	200	7000	TO-247AC	N-канал
IRGPC30KD2	600	23,0			TO-247AC	N-канал
IRGPC30MD2	600	26,0			TO-247AC	N-канал
IRGPC30U	600	23,0	100	3100	TO-247AC	N-канал
IRGPC40KD2	600	42,0	160	7000	TO-247AC	N-канал
IRGPC40U	600	42,0			TO-247AC	N-канал
IRGPC50KD2	600	52,0			TO-247AC	N-канал
IRGPC50MD2	600	60,0			TO-247AC	N-канал
IRGPC50U					TO-247AC	N-канал
IRGPF30F	900	20,0			TO-247AC	N-канал
IRGPH40F	900	31,0			TO-247AC	N-канал
IRGPH50F	900	51,0			TO-247AC	N-канал
IRGS14C40L	400	14,0				