


TOLERANCE = ±.010

COIL: @ 25°C  
 RESISTANCE 300 OHMS ± 10%  
 NOMINAL VOLTAGE 28.0 VDC  
 MUST OPERATE 13.0 VDC  
 MUST RELEASE 7.0 VDC MAX, 1.6 VDC MIN.

ENVIRONMENT:  
 VIBRATION 10 CPS TO 2000 CPS @ 20 g's  
 SHOCK 50 g's 11 MS. DURATION  
 TEMPERATURE -70 °C TO +125 °C

NOTES: OPERATE & RELEASE 10 MS MAX.  
OPERATE BOUNCE 2 MS MAX.  
RELEASE BOUNCE 5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: 10 AMPS 28 VDC,  
10 AMPS 115 VAC 400 HZ RESISTIVE  
100,000 OPERATIONS

DR. R.B. 9/14/98 CK.9/14/98

COMMUNICATIONS  
 INSTRUMENTS, INC.

CUST. GPL  
 CUST. NO. MS27245-1

TYPE '07' RELAY

B07D112BC4-0007