

M12 AUN-O

M12™ AIR-TIP™ UTILITY NOZZLE

- The M12™ powered utility nozzle is a great accessory that is designed to clean jobsite debris on short and medium hair carpeted surfaces
- The universal reception fits to all MILWAUKEE® M12™ and M18™ cordless vacs and covers most common hose sizes (31.8 mm, 47.6 mm and 63.5 mm)
- The M12™ powered brush with a 152 mm cleaning width gives a better cleaning than non-powered standard nozzles
- The curved skid plate on the M12™ powered floor tool rotates, allowing for easy back and forth motion, for a more enjoyable user experience
- Tool-less roller change for ease of troubleshooting
- LED light bar on the front of the unit lights up the cleaning pathway for better visibility
- Compatible with AIR-TIP™ trade focused vacuum accessories
- Premium 4-pole brushed motor, REDLITHIUM™ battery pack and REDLINK™ electronic delivering the needed power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M12™ batteries



REDLITHIUM™

Weight with battery pack (EPTA) (kg)	1.2 (M12 B2)
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article number	4932479461

