

# M12 GG-O

## M12™ SUB COMPACT GREASE GUN

- Powerful 12 V motor delivers over 562 bar max operating pressure
- REDLINK™ overload protection electronics in tool and battery pack deliver best in class system durability
- Extreme long run time - dispenses up to 7 cartridges per charge
- Strong handle balance and ergonomics - only 355 mm long and 3.2 kg
- Air bleeder valve - priming mechanism for quick flow
- Integrated hose storage & shoulder strap loop - added user convenience and reducing down time
- Three way loading - bulk, cartridge and suction capable
- Grease capacity 400 ml cartridge, 473 ml bulk
- Individual battery cell monitoring optimises tool run time and ensures long term pack durability
- On board fuel gauge and LED light
- REDLITHIUM™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life
- Flexible battery system: works with all MILWAUKEE® M12™ batteries
- Supplied with 914 mm x 14.4 mm high pressure flex hose with spring guard and grease coupler



### REDLITHIUM™

Pressure (bar)	562
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933440435

