




C3330R/C3340R

**Compact Tapered and Relieved
Head Side Cutters with Orange
PVC Handle**



PRODUCT DETAILS




- With tapered and relieved head
- Flush cut
- Orange PVC handles
- Screw joint that minimizes friction and maximizes jaw alignment
- Internal return spring with limited opening to prevent user hand fatigue
- High performance alloy steel
- Natural finish
- CNC machine grinding guarantees edge angle accuracy
- ISO 9654
- IP: Industrial pack



Follow the Fish!



PRODUCT ATTRIBUTES

Product	A	B	C	D	F			
C3330R	115 mm	11,7 mm	12,5 mm	6 mm	0.8 mm	0,3-1,25 mm	Flush	66 g
C3330R IP	115 mm	11,7 mm	12,5 mm	6 mm	0.8 mm	0,3-1,25 mm	Flush	66 g
C3340R	130 mm	13,8 mm	15,8 mm	8 mm	1.6 mm	0,4-1,6 mm	Flush	116 g
C3340R IP	130 mm	13,8 mm	15,8 mm	8 mm	1.6 mm	0.4-1.6 mm	Flush	116 g

Follow the Fish!



Contact: info@bahco.com / www.bahco.com