

# Aluminum master-slave PRO permanent socket strip 5+2-fold with overvoltage protection

Item-no.: 0615x00078001 (1,5 m cord)



Noble, transparent anodized aluminum case, matt

Built-in sockets (90° rotated), round

1,5 m power cord and angle plug (optional with 3 m or 5 m power cord)

1 blue master socket, 4 black slave sockets and 2 gray permanent sockets

Automatic electronic switching M/S with precisely adjustable switching threshold


Optical function display for M/S function

Acoustic fault message in case of overvoltage protection according to EN 61643-11 type 3

EHMANN advantage - the connected devices will remain in operation after release of overvoltage protection



Increased safety due to integrated child protection

End caps with mounting possibility and spare fuse



## Aluminum master-slave PRO permanent socket strip 5+2-fold with overvoltage protection

### Technical data

3.600 W Power	250 V ~ / 50 Hz Rated voltage	16 A Rated current
Power cord: H05VV-F 3G 1,5 mm <sup>2</sup> Plug: CEE 7/7 plug type EF, angular Sockets: Earthing contact type F Voltage U <sub>n</sub> : 230 V~ Max. continuous operation voltage U <sub>c</sub> : 255 V~ U <sub>oc</sub> : 5000 V Protection level Up: L-N < 1,0kV - L/N-PE < 1,5kV I <sub>max</sub> (8/20): 6,5 kA Fuse: T6,3AH/250 V SPD according to EN 61643-11: Type 3 Precise switching threshold: 7-100 W (master) Consumption: < 0,6 W Consumption overvoltage protection: < 0,1 W Safety class: IP20		
 <p>(similar illustration)</p>		
Item-no. 0615x00078001	EAN 401209600752 4	PU 10  586 x 65 x 44 mm Dimensions (L x W x H) 580 mm Fixing dimension