

Data Sheet

Triple Socket with 2 Power Sockets and 1 Power USB Socket

Item-no. 67335000 (BP)

Item-no.: 67335500 (SP)

02.10.2014

Voltage range: max. 30 Volt
Current load: max. 16 Ampere with 12 Volt
max. 10 Ampere with 24 Volt

Material Triple Socket:

Housing: Polycarbonat
Temperature stress: max. 135°C
Contact: Metal socket

Material Plug:

Housing. Polycarbonat
Temperature load : Max. 135 °C
Connection spring: Cu Sn 6
surface: shiny pickled
Contact spring: Cu Zn 37 F45
surface:: gal. Ni 5
Plug pin: Cu Zn 40 Pb 2
surface:: gal. Ni 5
Cable: flat cable 2.0m (2x1.5 mm²)

Triple Socket with 2 Power Sockets and 1 Power USB Socket

Item-no. 67334000 (BP)

Item-no.: 67334500 (SP)

USB Socket:

Input voltage:	8 - 34 Volt
Output voltage :	5 Volt
Output current max.:	5 A (2 x 2,5 A)
Input current duration:	4,4 A (2 x 2,2 A)
Current consumption:	< 5 mA (open circuit operation)
Overvoltage protection:	yes
Protection against overheating:	yes
Reverse voltage protection:	yes

