


Deep groove ball bearings, single row, shield on both sides



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
20	42	12	9,95	5	0,212	38000	19000	0,069	6004-2Z *



Calculation factors

k_r 0,025

f_0 14