

Tantalum Electrolytic Capacitors

CCC-01

(1 Flap FL16/20) 16 Values / 115 Pieces
Rectangular Plastic-Cases with radial leadwires

Type/Brand: T340 / Kemet

Tolerance: $\pm 20\%$

Temperature : -55 to +125°C

Values-Quantities Selection:

1,0uF/35V	20x	4,7uF/35V	10x	33uF/25V	4x	100uF/20V	5x
1,5uF/25V	5x	10 uF/25V	10x	47uF/ 6V	10x	150uF/16V	3x
2,2uF/35V	10x	22 uF/16V	8x	47uF/35V	5x	220uF/10V	3x
4,7uF/10V	10x	22 uF/35V	6x	68uF/16V	3x	330uF/ 6V	3x

CCC-02

(1 Flap FL16/10) 16 Values / 500 Pieces
Dipped Types with radial leadwires

Type/Brand: T350A / Kemet

Tolerance: $\pm 20\%$

Temperature: -55 to +85°C

Values-Quantities Selection:

0,10uF/35V	50x	1,0uF/35V	50x	4,7uF/35V	50x	15uF/20V	10x
0,22uF/35V	30x	1,5uF/35V	15x	6,8uF/35V	15x	22uF/16V	20x
0,47uF/35V	50x	2,2uF/35V	30x	10 uF/16V	50x	47uF/ 6V	15x
0,68uF/35V	25x	4,7uF/16V	50x	10 uF/35V	30x	100uF/3V	10x

Chip Tantalum Capacitors

SMC-02

(1 Flap FL24/10) 24 Values / 600 Pieces
Tantalum Electrolytic capacitors in chip form

Type/Brand: B45196 / Epcos

Tolerance: ±20%

Temperature: -55 to +125°C

Values-Quantities Selection:

0,10uF/35V (A)	40x	2,2uF/25V (B)	20x	6,8uF/20V (C)	20x	22uF/ 6V (C)	20x
0,22uF/35V (A)	20x	2,2uF/35V (C)	20x	6,8uF/35V (D)	10x	22uF/20V (D)	10x
0,47uF/35V (B)	40x	3,3uF/ 6V (A)	20x	10uF/ 6V (B)	40x	33uF/16V (D)	10x
1,0 uF/16V (A)	40x	4,7uF/16V (B)	20x	10uF/16V (C)	40x	47uF/10V (D)	40x
1,0 uF/35V (B)	40x	4,7uF/35V (D)	20x	10uF/35V (D)	40x	68uF/ 6V (D)	10x
2,2 uF/10V (A)	40x	6,8uF/10V (B)	20x	15uF/25V (D)	10x	100uF/ 4V (D)	10x