

KOA

RK73H1ETTP****F Flat Chip Resistors (Precision Grade) KIT

Ordner No : RK73H1E-KIT

- | | | | |
|-----------------------|---------------------|-----------------------------|---------------------------|
| • Technology | Thick film | • Resistor Values | 170 |
| • Package Inch / Size | 0402 / 1005 | • Resistor Pieces per value | 200 |
| • Series | E24 + Jumper | • Operating Temperature | -55 to +155 |
| • Resistor Range | 1Ω to 10MΩ + Jumper | • Temperature Coefficient | 1Ω to 9.76Ω : ±200 ppm |
| • Tolerance | ±1 % | | 10Ω to 1MΩ : ±100 ppm |
| • Maximum Wattage | 0.1 W | | 1.02MΩ to 10MΩ : ±200 ppm |
| • Maximum Voltage | 50 V | | |



Binder Dim. : 250×300×35 mm
Weight. : 1450 g

KIT Content Listings

No	Manufacturer part number	Resistance
1	RK73Z1ETTP	0 Ω
2	RK73H1ETTP1R00F	1 Ω
3	RK73H1ETTP1R10F	1.1 Ω
4	RK73H1ETTP1R20F	1.2 Ω
5	RK73H1ETTP1R30F	1.3 Ω
6	RK73H1ETTP1R50F	1.5 Ω
7	RK73H1ETTP1R60F	1.6 Ω
8	RK73H1ETTP1R80F	1.8 Ω
9	RK73H1ETTP2R00F	2 Ω
10	RK73H1ETTP2R20F	2.2 Ω
11	RK73H1ETTP2R40F	2.4 Ω
12	RK73H1ETTP2R70F	2.7 Ω
13	RK73H1ETTP3R00F	3 Ω
14	RK73H1ETTP3R30F	3.3 Ω
15	RK73H1ETTP3R60F	3.6 Ω
16	RK73H1ETTP3R90F	3.9 Ω
17	RK73H1ETTP4R30F	4.3 Ω
18	RK73H1ETTP4R70F	4.7 Ω
19	RK73H1ETTP5R10F	5.1 Ω
20	RK73H1ETTP5R60F	5.6 Ω
21	RK73H1ETTP6R20F	6.2 Ω
22	RK73H1ETTP6R80F	6.8 Ω
23	RK73H1ETTP7R50F	7.5 Ω
24	RK73H1ETTP8R20F	8.2 Ω
25	RK73H1ETTP9R10F	9.1 Ω
26	RK73H1ETTP10R0F	10 Ω
27	RK73H1ETTP11R0F	11 Ω
28	RK73H1ETTP12R0F	12 Ω
29	RK73H1ETTP13R0F	13 Ω
30	RK73H1ETTP15R0F	15 Ω
31	RK73H1ETTP16R0F	16 Ω
32	RK73H1ETTP18R0F	18 Ω
33	RK73H1ETTP20R0F	20 Ω
34	RK73H1ETTP22R0F	22 Ω
35	RK73H1ETTP24R0F	24 Ω
36	RK73H1ETTP27R0F	27 Ω
37	RK73H1ETTP30R0F	30 Ω
38	RK73H1ETTP33R0F	33 Ω
39	RK73H1ETTP36R0F	36 Ω
40	RK73H1ETTP39R0F	39 Ω
41	RK73H1ETTP43R0F	43 Ω
42	RK73H1ETTP47R0F	47 Ω
43	RK73H1ETTP51R0F	51 Ω
44	RK73H1ETTP56R0F	56 Ω
45	RK73H1ETTP62R0F	62 Ω
46	RK73H1ETTP68R0F	68 Ω
47	RK73H1ETTP75R0F	75 Ω
48	RK73H1ETTP82R0F	82 Ω
49	RK73H1ETTP91R0F	91 Ω
50	RK73H1ETTP1000F	100 Ω
51	RK73H1ETTP1100F	110 Ω
52	RK73H1ETTP1200F	120 Ω
53	RK73H1ETTP1300F	130 Ω
54	RK73H1ETTP1500F	150 Ω
55	RK73H1ETTP1600F	160 Ω
56	RK73H1ETTP1800F	180 Ω
57	RK73H1ETTP2000F	200 Ω
58	RK73H1ETTP2200F	220 Ω
59	RK73H1ETTP2400F	240 Ω
60	RK73H1ETTP2700F	270 Ω

No	Manufacturer part number	Resistance
61	RK73H1ETTP3000F	300 Ω
62	RK73H1ETTP3300F	330 Ω
63	RK73H1ETTP3600F	360 Ω
64	RK73H1ETTP3900F	390 Ω
65	RK73H1ETTP4300F	430 Ω
66	RK73H1ETTP4700F	470 Ω
67	RK73H1ETTP5100F	510 Ω
68	RK73H1ETTP5600F	560 Ω
69	RK73H1ETTP6200F	620 Ω
70	RK73H1ETTP6800F	680 Ω
71	RK73H1ETTP7500F	750 Ω
72	RK73H1ETTP8200F	820 Ω
73	RK73H1ETTP9100F	910 Ω
74	RK73H1ETTP1001F	1 kΩ
75	RK73H1ETTP1101F	1.1 kΩ
76	RK73H1ETTP1201F	1.2 kΩ
77	RK73H1ETTP1301F	1.3 kΩ
78	RK73H1ETTP1501F	1.5 kΩ
79	RK73H1ETTP1601F	1.6 kΩ
80	RK73H1ETTP1801F	1.8 kΩ
81	RK73H1ETTP2001F	2 kΩ
82	RK73H1ETTP2201F	2.2 kΩ
83	RK73H1ETTP2401F	2.4 kΩ
84	RK73H1ETTP2701F	2.7 kΩ
85	RK73H1ETTP3001F	3 kΩ
86	RK73H1ETTP3301F	3.3 kΩ
87	RK73H1ETTP3601F	3.6 kΩ
88	RK73H1ETTP3901F	3.9 kΩ
89	RK73H1ETTP4301F	4.3 kΩ
90	RK73H1ETTP4701F	4.7 kΩ
91	RK73H1ETTP5101F	5.1 kΩ
92	RK73H1ETTP5601F	5.6 kΩ
93	RK73H1ETTP6201F	6.2 kΩ
94	RK73H1ETTP6801F	6.8 kΩ
95	RK73H1ETTP7501F	7.5 kΩ
96	RK73H1ETTP8201F	8.2 kΩ
97	RK73H1ETTP9101F	9.1 kΩ
98	RK73H1ETTP1002F	10 kΩ
99	RK73H1ETTP1102F	11 kΩ
100	RK73H1ETTP1202F	12 kΩ
101	RK73H1ETTP1302F	13 kΩ
102	RK73H1ETTP1502F	15 kΩ
103	RK73H1ETTP1602F	16 kΩ
104	RK73H1ETTP1802F	18 kΩ
105	RK73H1ETTP2002F	20 kΩ
106	RK73H1ETTP2202F	22 kΩ
107	RK73H1ETTP2402F	24 kΩ
108	RK73H1ETTP2702F	27 kΩ
109	RK73H1ETTP3002F	30 kΩ
110	RK73H1ETTP3302F	33 kΩ
111	RK73H1ETTP3602F	36 kΩ
112	RK73H1ETTP3902F	39 kΩ
113	RK73H1ETTP4302F	43 kΩ
114	RK73H1ETTP4702F	47 kΩ
115	RK73H1ETTP5102F	51 kΩ
116	RK73H1ETTP5602F	56 kΩ
117	RK73H1ETTP6202F	62 kΩ
118	RK73H1ETTP6802F	68 kΩ
119	RK73H1ETTP7502F	75 kΩ
120	RK73H1ETTP8202F	82 kΩ

No	Manufacturer part number	Resistance
121	RK73H1ETTP9102F	91 kΩ
122	RK73H1ETTP1003F	100 kΩ
123	RK73H1ETTP1103F	110 kΩ
124	RK73H1ETTP1203F	120 kΩ
125	RK73H1ETTP1303F	130 kΩ
126	RK73H1ETTP1503F	150 kΩ
127	RK73H1ETTP1603F	160 kΩ
128	RK73H1ETTP1803F	180 kΩ
129	RK73H1ETTP2003F	200 kΩ
130	RK73H1ETTP2203F	220 kΩ
131	RK73H1ETTP2403F	240 kΩ
132	RK73H1ETTP2703F	270 kΩ
133	RK73H1ETTP3003F	300 kΩ
134	RK73H1ETTP3303F	330 kΩ
135	RK73H1ETTP3603F	360 kΩ
136	RK73H1ETTP3903F	390 kΩ
137	RK73H1ETTP4303F	430 kΩ
138	RK73H1ETTP4703F	470 kΩ
139	RK73H1ETTP5103F	510 kΩ
140	RK73H1ETTP5603F	560 kΩ
141	RK73H1ETTP6203F	620 kΩ
142	RK73H1ETTP6803F	680 kΩ
143	RK73H1ETTP7503F	750 kΩ
144	RK73H1ETTP8203F	820 kΩ
145	RK73H1ETTP9103F	910 kΩ
146	RK73H1ETTP1004F	1 MΩ
147	RK73H1ETTP1104F	1.1 MΩ
148	RK73H1ETTP1204F	1.2 MΩ
149	RK73H1ETTP1304F	1.3 MΩ
150	RK73H1ETTP1504F	1.5 MΩ
151	RK73H1ETTP1604F	1.6 MΩ
152	RK73H1ETTP1804F	1.8 MΩ
153	RK73H1ETTP2004F	2 MΩ
154	RK73H1ETTP2204F	2.2 MΩ
155	RK73H1ETTP2404F	2.4 MΩ
156	RK73H1ETTP2704F	2.7 MΩ
157	RK73H1ETTP3004F	3 MΩ
158	RK73H1ETTP3304F	3.3 MΩ
159	RK73H1ETTP3604F	3.6 MΩ
160	RK73H1ETTP3904F	3.9 MΩ
161	RK73H1ETTP4304F	4.3 MΩ
162	RK73H1ETTP4704F	4.7 MΩ
163	RK73H1ETTP5104F	5.1 MΩ
164	RK73H1ETTP5604F	5.6 MΩ
165	RK73H1ETTP6204F	6.2 MΩ
166	RK73H1ETTP6804F	6.8 MΩ
167	RK73H1ETTP7504F	7.5 MΩ
168	RK73H1ETTP8204F	8.2 MΩ
169	RK73H1ETTP9104F	9.1 MΩ
170	RK73H1ETTP1005F	10 MΩ

KOA

RK73H1JTTD****F Flat Chip Resistors (Precision Grade) KIT

Ordner No : RK73H1J-KIT

- Technology Thick film
- Resistor Values 170
- Package Inch / Size 0603 / 1608
- Resistor Pieces per value 100
- Series E24 + Jumper
- Operating Temperature -55 to +155
- Resistor Range 1Ω to 10MΩ + Jumper
- Temperature Coefficient 1Ω to 9.76Ω : ±200 ppm
- Tolerance ±1 %
- Maximum Wattage 0.1 W
- Maximum Voltage 50 V
- Temperature Coefficient 10Ω to 1MΩ : ±100 ppm
- Temperature Coefficient 1.02MΩ to 10MΩ : ±200 ppm



Binder Dim. : 250x300x35 mm
Weight. : 1450 g

KIT Content Listings

No	Manufacturer part number	Resistance
1	RK73Z1JTTD	0 Ω
2	RK73H1JTTD1R00F	1 Ω
3	RK73H1JTTD1R10F	1.1 Ω
4	RK73H1JTTD1R20F	1.2 Ω
5	RK73H1JTTD1R30F	1.3 Ω
6	RK73H1JTTD1R50F	1.5 Ω
7	RK73H1JTTD1R60F	1.6 Ω
8	RK73H1JTTD1R80F	1.8 Ω
9	RK73H1JTTD2R00F	2 Ω
10	RK73H1JTTD2R20F	2.2 Ω
11	RK73H1JTTD2R40F	2.4 Ω
12	RK73H1JTTD2R70F	2.7 Ω
13	RK73H1JTTD3R00F	3 Ω
14	RK73H1JTTD3R30F	3.3 Ω
15	RK73H1JTTD3R60F	3.6 Ω
16	RK73H1JTTD3R90F	3.9 Ω
17	RK73H1JTTD4R30F	4.3 Ω
18	RK73H1JTTD4R70F	4.7 Ω
19	RK73H1JTTD5R10F	5.1 Ω
20	RK73H1JTTD5R60F	5.6 Ω
21	RK73H1JTTD6R20F	6.2 Ω
22	RK73H1JTTD6R80F	6.8 Ω
23	RK73H1JTTD7R50F	7.5 Ω
24	RK73H1JTTD8R20F	8.2 Ω
25	RK73H1JTTD9R10F	9.1 Ω
26	RK73H1JTTD10R0F	10 Ω
27	RK73H1JTTD11R0F	11 Ω
28	RK73H1JTTD12R0F	12 Ω
29	RK73H1JTTD13R0F	13 Ω
30	RK73H1JTTD15R0F	15 Ω
31	RK73H1JTTD16R0F	16 Ω
32	RK73H1JTTD18R0F	18 Ω
33	RK73H1JTTD20R0F	20 Ω
34	RK73H1JTTD22R0F	22 Ω
35	RK73H1JTTD24R0F	24 Ω
36	RK73H1JTTD27R0F	27 Ω
37	RK73H1JTTD30R0F	30 Ω
38	RK73H1JTTD33R0F	33 Ω
39	RK73H1JTTD36R0F	36 Ω
40	RK73H1JTTD39R0F	39 Ω
41	RK73H1JTTD43R0F	43 Ω
42	RK73H1JTTD47R0F	47 Ω
43	RK73H1JTTD51R0F	51 Ω
44	RK73H1JTTD56R0F	56 Ω
45	RK73H1JTTD62R0F	62 Ω
46	RK73H1JTTD68R0F	68 Ω
47	RK73H1JTTD75R0F	75 Ω
48	RK73H1JTTD82R0F	82 Ω
49	RK73H1JTTD91R0F	91 Ω
50	RK73H1JTTD1000F	100 Ω
51	RK73H1JTTD1100F	110 Ω
52	RK73H1JTTD1200F	120 Ω
53	RK73H1JTTD1300F	130 Ω
54	RK73H1JTTD1500F	150 Ω
55	RK73H1JTTD1600F	160 Ω
56	RK73H1JTTD1800F	180 Ω
57	RK73H1JTTD2000F	200 Ω
58	RK73H1JTTD2200F	220 Ω
59	RK73H1JTTD2400F	240 Ω
60	RK73H1JTTD2700F	270 Ω

No	Manufacturer part number	Resistance
61	RK73H1JTTD3000F	300 Ω
62	RK73H1JTTD3300F	330 Ω
63	RK73H1JTTD3600F	360 Ω
64	RK73H1JTTD3900F	390 Ω
65	RK73H1JTTD4300F	430 Ω
66	RK73H1JTTD4700F	470 Ω
67	RK73H1JTTD5100F	510 Ω
68	RK73H1JTTD5600F	560 Ω
69	RK73H1JTTD6200F	620 Ω
70	RK73H1JTTD6800F	680 Ω
71	RK73H1JTTD7500F	750 Ω
72	RK73H1JTTD8200F	820 Ω
73	RK73H1JTTD9100F	910 Ω
74	RK73H1JTTD1001F	1 kΩ
75	RK73H1JTTD1101F	1.1 kΩ
76	RK73H1JTTD1201F	1.2 kΩ
77	RK73H1JTTD1301F	1.3 kΩ
78	RK73H1JTTD1501F	1.5 kΩ
79	RK73H1JTTD1601F	1.6 kΩ
80	RK73H1JTTD1801F	1.8 kΩ
81	RK73H1JTTD2001F	2 kΩ
82	RK73H1JTTD2201F	2.2 kΩ
83	RK73H1JTTD2401F	2.4 kΩ
84	RK73H1JTTD2701F	2.7 kΩ
85	RK73H1JTTD3001F	3 kΩ
86	RK73H1JTTD3301F	3.3 kΩ
87	RK73H1JTTD3601F	3.6 kΩ
88	RK73H1JTTD3901F	3.9 kΩ
89	RK73H1JTTD4301F	4.3 kΩ
90	RK73H1JTTD4701F	4.7 kΩ
91	RK73H1JTTD5101F	5.1 kΩ
92	RK73H1JTTD5601F	5.6 kΩ
93	RK73H1JTTD6201F	6.2 kΩ
94	RK73H1JTTD6801F	6.8 kΩ
95	RK73H1JTTD7501F	7.5 kΩ
96	RK73H1JTTD8201F	8.2 kΩ
97	RK73H1JTTD9101F	9.1 kΩ
98	RK73H1JTTD1002F	10 kΩ
99	RK73H1JTTD1102F	11 kΩ
100	RK73H1JTTD1202F	12 kΩ
101	RK73H1JTTD1302F	13 kΩ
102	RK73H1JTTD1502F	15 kΩ
103	RK73H1JTTD1602F	16 kΩ
104	RK73H1JTTD1802F	18 kΩ
105	RK73H1JTTD2002F	20 kΩ
106	RK73H1JTTD2202F	22 kΩ
107	RK73H1JTTD2402F	24 kΩ
108	RK73H1JTTD2702F	27 kΩ
109	RK73H1JTTD3002F	30 kΩ
110	RK73H1JTTD3302F	33 kΩ
111	RK73H1JTTD3602F	36 kΩ
112	RK73H1JTTD3902F	39 kΩ
113	RK73H1JTTD4302F	43 kΩ
114	RK73H1JTTD4702F	47 kΩ
115	RK73H1JTTD5102F	51 kΩ
116	RK73H1JTTD5602F	56 kΩ
117	RK73H1JTTD6202F	62 kΩ
118	RK73H1JTTD6802F	68 kΩ
119	RK73H1JTTD7502F	75 kΩ
120	RK73H1JTTD8202F	82 kΩ

No	Manufacturer part number	Resistance
121	RK73H1JTTD9102F	91 kΩ
122	RK73H1JTTD1003F	100 kΩ
123	RK73H1JTTD1103F	110 kΩ
124	RK73H1JTTD1203F	120 kΩ
125	RK73H1JTTD1303F	130 kΩ
126	RK73H1JTTD1503F	150 kΩ
127	RK73H1JTTD1603F	160 kΩ
128	RK73H1JTTD1803F	180 kΩ
129	RK73H1JTTD2003F	200 kΩ
130	RK73H1JTTD2203F	220 kΩ
131	RK73H1JTTD2403F	240 kΩ
132	RK73H1JTTD2703F	270 kΩ
133	RK73H1JTTD3003F	300 kΩ
134	RK73H1JTTD3303F	330 kΩ
135	RK73H1JTTD3603F	360 kΩ
136	RK73H1JTTD3903F	390 kΩ
137	RK73H1JTTD4303F	430 kΩ
138	RK73H1JTTD4703F	470 kΩ
139	RK73H1JTTD5103F	510 kΩ
140	RK73H1JTTD5603F	560 kΩ
141	RK73H1JTTD6203F	620 kΩ
142	RK73H1JTTD6803F	680 kΩ
143	RK73H1JTTD7503F	750 kΩ
144	RK73H1JTTD8203F	820 kΩ
145	RK73H1JTTD9103F	910 kΩ
146	RK73H1JTTD1004F	1 MΩ
147	RK73H1JTTD1104F	1.1 MΩ
148	RK73H1JTTD1204F	1.2 MΩ
149	RK73H1JTTD1304F	1.3 MΩ
150	RK73H1JTTD1504F	1.5 MΩ
151	RK73H1JTTD1604F	1.6 MΩ
152	RK73H1JTTD1804F	1.8 MΩ
153	RK73H1JTTD2004F	2 MΩ
154	RK73H1JTTD2204F	2.2 MΩ
155	RK73H1JTTD2404F	2.4 MΩ
156	RK73H1JTTD2704F	2.7 MΩ
157	RK73H1JTTD3004F	3 MΩ
158	RK73H1JTTD3304F	3.3 MΩ
159	RK73H1JTTD3604F	3.6 MΩ
160	RK73H1JTTD3904F	3.9 MΩ
161	RK73H1JTTD4304F	4.3 MΩ
162	RK73H1JTTD4704F	4.7 MΩ
163	RK73H1JTTD5104F	5.1 MΩ
164	RK73H1JTTD5604F	5.6 MΩ
165	RK73H1JTTD6204F	6.2 MΩ
166	RK73H1JTTD6804F	6.8 MΩ
167	RK73H1JTTD7504F	7.5 MΩ
168	RK73H1JTTD8204F	8.2 MΩ
169	RK73H1JTTD9104F	9.1 MΩ
170	RK73H1JTTD1005F	10 MΩ

KOA

RK73H2ATTD****F Flat Chip Resistors (Precision Grade) KIT

Ordner No : RK73H2A-KIT

- Technology Thick film
- Resistor Values 170
- Package Inch / Size 0805 / 2012
- Resistor Pieces per value 100
- Series E24 + Jumper
- Operating Temperature -55 to +155
- Resistor Range 1Ω to 10MΩ + Jumper
- Temperature Coefficient
- Tolerance ±1 %
- Maximum Wattage 0.25 W
- Maximum Voltage 150 V
- Resistor Values 170
- Resistor Pieces per value 100
- Operating Temperature -55 to +155
- Temperature Coefficient
- Resistor Range 1Ω to 9.76Ω : ±200 ppm
- 10Ω to 1MΩ : ±100 ppm
- 1.02MΩ to 10MΩ : ±400 ppm



Binder Dim. : 250×300×35 mm
Weight. : 1450 g

KIT Content Listings

No	Manufacturer part number	Resistance
1	RK73Z2ATTD	0 Ω
2	RK73H2ATTD1R00F	1 Ω
3	RK73H2ATTD1R10F	1.1 Ω
4	RK73H2ATTD1R20F	1.2 Ω
5	RK73H2ATTD1R30F	1.3 Ω
6	RK73H2ATTD1R50F	1.5 Ω
7	RK73H2ATTD1R60F	1.6 Ω
8	RK73H2ATTD1R80F	1.8 Ω
9	RK73H2ATTD2R00F	2 Ω
10	RK73H2ATTD2R20F	2.2 Ω
11	RK73H2ATTD2R40F	2.4 Ω
12	RK73H2ATTD2R70F	2.7 Ω
13	RK73H2ATTD3R00F	3 Ω
14	RK73H2ATTD3R30F	3.3 Ω
15	RK73H2ATTD3R60F	3.6 Ω
16	RK73H2ATTD3R90F	3.9 Ω
17	RK73H2ATTD4R30F	4.3 Ω
18	RK73H2ATTD4R70F	4.7 Ω
19	RK73H2ATTD5R10F	5.1 Ω
20	RK73H2ATTD5R60F	5.6 Ω
21	RK73H2ATTD6R20F	6.2 Ω
22	RK73H2ATTD6R80F	6.8 Ω
23	RK73H2ATTD7R50F	7.5 Ω
24	RK73H2ATTD8R20F	8.2 Ω
25	RK73H2ATTD9R10F	9.1 Ω
26	RK73H2ATTD10R0F	10 Ω
27	RK73H2ATTD11R0F	11 Ω
28	RK73H2ATTD12R0F	12 Ω
29	RK73H2ATTD13R0F	13 Ω
30	RK73H2ATTD15R0F	15 Ω
31	RK73H2ATTD16R0F	16 Ω
32	RK73H2ATTD18R0F	18 Ω
33	RK73H2ATTD20R0F	20 Ω
34	RK73H2ATTD22R0F	22 Ω
35	RK73H2ATTD24R0F	24 Ω
36	RK73H2ATTD27R0F	27 Ω
37	RK73H2ATTD30R0F	30 Ω
38	RK73H2ATTD33R0F	33 Ω
39	RK73H2ATTD36R0F	36 Ω
40	RK73H2ATTD39R0F	39 Ω
41	RK73H2ATTD43R0F	43 Ω
42	RK73H2ATTD47R0F	47 Ω
43	RK73H2ATTD51R0F	51 Ω
44	RK73H2ATTD56R0F	56 Ω
45	RK73H2ATTD62R0F	62 Ω
46	RK73H2ATTD68R0F	68 Ω
47	RK73H2ATTD75R0F	75 Ω
48	RK73H2ATTD82R0F	82 Ω
49	RK73H2ATTD91R0F	91 Ω
50	RK73H2ATTD1000F	100 Ω
51	RK73H2ATTD1100F	110 Ω
52	RK73H2ATTD1200F	120 Ω
53	RK73H2ATTD1300F	130 Ω
54	RK73H2ATTD1500F	150 Ω
55	RK73H2ATTD1600F	160 Ω
56	RK73H2ATTD1800F	180 Ω
57	RK73H2ATTD2000F	200 Ω
58	RK73H2ATTD2200F	220 Ω
59	RK73H2ATTD2400F	240 Ω
60	RK73H2ATTD2700F	270 Ω

No	Manufacturer part number	Resistance
61	RK73H2ATTD3000F	300 Ω
62	RK73H2ATTD3300F	330 Ω
63	RK73H2ATTD3600F	360 Ω
64	RK73H2ATTD3900F	390 Ω
65	RK73H2ATTD4300F	430 Ω
66	RK73H2ATTD4700F	470 Ω
67	RK73H2ATTD5100F	510 Ω
68	RK73H2ATTD5600F	560 Ω
69	RK73H2ATTD6200F	620 Ω
70	RK73H2ATTD6800F	680 Ω
71	RK73H2ATTD7500F	750 Ω
72	RK73H2ATTD8200F	820 Ω
73	RK73H2ATTD9100F	910 Ω
74	RK73H2ATTD1001F	1 kΩ
75	RK73H2ATTD1101F	1.1 kΩ
76	RK73H2ATTD1201F	1.2 kΩ
77	RK73H2ATTD1301F	1.3 kΩ
78	RK73H2ATTD1501F	1.5 kΩ
79	RK73H2ATTD1601F	1.6 kΩ
80	RK73H2ATTD1801F	1.8 kΩ
81	RK73H2ATTD2001F	2 kΩ
82	RK73H2ATTD2201F	2.2 kΩ
83	RK73H2ATTD2401F	2.4 kΩ
84	RK73H2ATTD2701F	2.7 kΩ
85	RK73H2ATTD3001F	3 kΩ
86	RK73H2ATTD3301F	3.3 kΩ
87	RK73H2ATTD3601F	3.6 kΩ
88	RK73H2ATTD3901F	3.9 kΩ
89	RK73H2ATTD4301F	4.3 kΩ
90	RK73H2ATTD4701F	4.7 kΩ
91	RK73H2ATTD5101F	5.1 kΩ
92	RK73H2ATTD5601F	5.6 kΩ
93	RK73H2ATTD6201F	6.2 kΩ
94	RK73H2ATTD6801F	6.8 kΩ
95	RK73H2ATTD7501F	7.5 kΩ
96	RK73H2ATTD8201F	8.2 kΩ
97	RK73H2ATTD9101F	9.1 kΩ
98	RK73H2ATTD1002F	10 kΩ
99	RK73H2ATTD1102F	11 kΩ
100	RK73H2ATTD1202F	12 kΩ
101	RK73H2ATTD1302F	13 kΩ
102	RK73H2ATTD1502F	15 kΩ
103	RK73H2ATTD1602F	16 kΩ
104	RK73H2ATTD1802F	18 kΩ
105	RK73H2ATTD2002F	20 kΩ
106	RK73H2ATTD2202F	22 kΩ
107	RK73H2ATTD2402F	24 kΩ
108	RK73H2ATTD2702F	27 kΩ
109	RK73H2ATTD3002F	30 kΩ
110	RK73H2ATTD3302F	33 kΩ
111	RK73H2ATTD3602F	36 kΩ
112	RK73H2ATTD3902F	39 kΩ
113	RK73H2ATTD4302F	43 kΩ
114	RK73H2ATTD4702F	47 kΩ
115	RK73H2ATTD5102F	51 kΩ
116	RK73H2ATTD5602F	56 kΩ
117	RK73H2ATTD6202F	62 kΩ
118	RK73H2ATTD6802F	68 kΩ
119	RK73H2ATTD7502F	75 kΩ
120	RK73H2ATTD8202F	82 kΩ

No	Manufacturer part number	Resistance
121	RK73H2ATTD9102F	91 kΩ
122	RK73H2ATTD1003F	100 kΩ
123	RK73H2ATTD1103F	110 kΩ
124	RK73H2ATTD1203F	120 kΩ
125	RK73H2ATTD1303F	130 kΩ
126	RK73H2ATTD1503F	150 kΩ
127	RK73H2ATTD1603F	160 kΩ
128	RK73H2ATTD1803F	180 kΩ
129	RK73H2ATTD2003F	200 kΩ
130	RK73H2ATTD2203F	220 kΩ
131	RK73H2ATTD2403F	240 kΩ
132	RK73H2ATTD2703F	270 kΩ
133	RK73H2ATTD3003F	300 kΩ
134	RK73H2ATTD3303F	330 kΩ
135	RK73H2ATTD3603F	360 kΩ
136	RK73H2ATTD3903F	390 kΩ
137	RK73H2ATTD4303F	430 kΩ
138	RK73H2ATTD4703F	470 kΩ
139	RK73H2ATTD5103F	510 kΩ
140	RK73H2ATTD5603F	560 kΩ
141	RK73H2ATTD6203F	620 kΩ
142	RK73H2ATTD6803F	680 kΩ
143	RK73H2ATTD7503F	750 kΩ
144	RK73H2ATTD8203F	820 kΩ
145	RK73H2ATTD9103F	910 kΩ
146	RK73H2ATTD1004F	1 MΩ
147	RK73H2ATTD1104F	1.1 MΩ
148	RK73H2ATTD1204F	1.2 MΩ
149	RK73H2ATTD1304F	1.3 MΩ
150	RK73H2ATTD1504F	1.5 MΩ
151	RK73H2ATTD1604F	1.6 MΩ
152	RK73H2ATTD1804F	1.8 MΩ
153	RK73H2ATTD2004F	2 MΩ
154	RK73H2ATTD2204F	2.2 MΩ
155	RK73H2ATTD2404F	2.4 MΩ
156	RK73H2ATTD2704F	2.7 MΩ
157	RK73H2ATTD3004F	3 MΩ
158	RK73H2ATTD3304F	3.3 MΩ
159	RK73H2ATTD3604F	3.6 MΩ
160	RK73H2ATTD3904F	3.9 MΩ
161	RK73H2ATTD4304F	4.3 MΩ
162	RK73H2ATTD4704F	4.7 MΩ
163	RK73H2ATTD5104F	5.1 MΩ
164	RK73H2ATTD5604F	5.6 MΩ
165	RK73H2ATTD6204F	6.2 MΩ
166	RK73H2ATTD6804F	6.8 MΩ
167	RK73H2ATTD7504F	7.5 MΩ
168	RK73H2ATTD8204F	8.2 MΩ
169	RK73H2ATTD9104F	9.1 MΩ
170	RK73H2ATTD1005F	10 MΩ