



1 2 3 4 5 6

A


B

C

D



Abisolierlänge: 13mm  
 stripping length: 13mm  
 Anzugsmoment: 10mm<sup>2</sup> 16mm<sup>2</sup> 25mm<sup>2</sup>  
 Tightning torque: 6Nm 6Nm 7Nm  
 für Litze 10-25mm<sup>2</sup>, AWG 6-4, feindrähtig  
 for stranded wire 10-25mm<sup>2</sup>, AWG 6-4, fine wire



ALL Dimensions in mm Original Size DIN A 4		Techn. Character.			Nicht tolerierte Maß/Free size tolerances	
			Dat.	Name	Maßstab/Scale 2:1	100A Axialschraubkontakt Buchse 100A axial screw contact, female 10-25mm <sup>2</sup> versilbert/silver plated
		Detail.	15.07.11	gru		
		Insp.		Rü		
		Stand.				
A		HARTING Electric GmbH & Co. KG D-32339 Espelkamp				TB 09 11 000 6212
Mod.	Dat.	Name				