

860H - Dinging hammers, round face





Standards:

NF ISO 15601, ISO 15601

Description:

- High safety hickory handle, triple fit: 2 steel wedges and 1 wood wedge.



	Length L [mm]	Length L1 [mm]	Handle ["]	Weight [g]	Diameter [mm]
860H.26	297.0	114.0	210.MHB26	340.0	26.0
860H.28	297.0	118.0	210.MHB26	370.0	28.0
860H.30	314.0	123.0	210.MHB28	440.0	30.0
860H.32	339.0	134.0	210.MHB29	570.0	32.0
860H.36	339.0	139.0	210.MHB29	700.0	36.0
860H.40	377.0	149.0	210.MHB31	920.0	40.0