

DABP080806GE Terminal box, 80x82x56

The ABS terminal box range, DABP, with a IP 66, 67 protection degree, is available off the shelf in many different sizes. The DABP range is well suited for demanding environments, since water and dust are prevented from entering the terminal box, thus eliminating the risk for component failure, and with that unnecessary downtime.

Feature:
IP 66,67 IK 06/07

CE UKCA GOST



CHARACTERISTICS

Height	80 mm
Width	82 mm
Depth	56 mm
Inner depth (mm)	42
Weight (kg)	0.10

Item no.: DABP080806GE
EAN no.: 6418677177354

Technical data

Description: ABS box, halogen-free, suitable for indoor use. Low UV radiation resistance.

Material: Body: ABS. Plain cover: ABS. Transparent cover: polycarbonate.

Gasket: Polyurethane gasket integrated in the box cover.

Temperature resistance: -40 °C to +60 °C.

Flammability: UL94 HB.

Protection: IP 66, 67 | IK 06 (-25 °C), IK 07 (+35 °C).

Finish: RAL 7035.

Delivery: Body, cover, cover screws manufactured from stainless steel, mounting screws and cover plugs made from polyamide.

Features

Feature: ABS terminal box, available in a wide range of sizes, with a high IP 66, 67 protection degree.

Advantage: Customers can choose terminal boxes that meet their size requirements, off the shelf. The installed components inside the terminal box will be safe and secure due to the high protection degree.

Benefit: Customers can receive terminal boxes with a short delivery time, that match their size requirements. This will also remove any extra costs due to oversizing. Component failure and unnecessary downtime is avoided as water and dust are prevented from entering the terminal box.

Comment: The mounting plate, DMP, and DIN profiles, DR, have to be ordered separately, in order to complete the installation of the terminal box.