




### 19"-shelf 1 U "VARIp lain" with 19" mounting



- fixed mounting
- depth variable due to VARIp lain technology
- telescopic: 445 - 780 mm (see figure)
- easy one-man installation due to open long hole in the 19" front (hinged)

**Material:**

sheet metal 2 mm

**Finish:**


RAL 7035 light grey

**Load capacity:**

150 kg (distributed load)

Order no.
316-036-99

### Shelf 1 U for cabinets with 19" mounting, extractable, 1,5 U



- extractable
- ventilated
- high quality telescopic rails with maximum extension, hold-in and disconnect
- includes assembly material
- mounting to 19" level
- Space requirement (height) approx. 1.5 U

**Material:**

sheet metal 1,5 mm

**Finish:**


RAL 7035 light grey

**Load capacity:**

approx. 40 kg

D mm	d mm	Order no.
600	465	110-876-10
800	665	110-877-12

### Shelf 1 U for cabinets without 19" mounting, 1,5 U



- fixed installation or extractable (high quality telescopic rails with maximum extension, hold-in and disconnect)
- for depths D=600 mm and D=800 mm
- ventilated
- includes assembly material
- can only be mounted to the rack
- Space requirement (height) approx. 1.5 U

**Material:**

sheet metal 1,5 mm

**Finish:**


RAL 7035 light grey

**Load capacity:**

approx. 40 kg

Description	Order no.
fixed	110-870-10
extractable	110-873-10

### Shelf, for cabinets with only one 19" vertical level



- fixed installation
- mounts easily onto the front or rear 19" mounting brackets
- ventilated
- incl. assembly material

**Material:**

sheet metal 1,5 mm

**Finish:**

RAL 7035 light grey

**Load capacity:**

15 kg

U	Order no.
2	315-810-20
3	315-810-00