Mini free-standing Beacons / LED-Permanent Light 204 LED Perm. Beacon WM 24VAC/DC RD



i

Part No.: 204.100.75



MECHANICAL DATA	
Height	107 mm
Diameter	58 mm
Materials	PA-GF PC
Dome colour	Red
Housing colour	Black
Protection category	IP65
Connection	Spring-type terminal
cross-sectional area maximum	2,50mm² / 14AWG
Cable entry	Screwed cable gland
Cable entry minimum	d = 3 mm
Cable entry maximum	d = 6 mm
Tension relief	Present (conforms to VDE)
Type of fixing	Wall mounting
Working temperature minimum	-20°C
Working temperature maximum	+50°C
Weight with packaging	100 g
Product weight	71 g
ELECTRICAL DATA	
Operating voltage	24V
Operating voltage type	AC/DC
Operating voltage frequency	50Hz
Operating voltage frequency Operating voltage tolerance	50Hz +/- 10%
Operating voltage tolerance	+/- 10%
Operating voltage tolerance Rated operational voltage	+/- 10% 24 VDC
Operating voltage tolerance Rated operational voltage Rated operational current	+/- 10% 24 VDC 45 mA
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current	+/- 10% 24 VDC 45 mA 500 mA
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class	+/- 10% 24 VDC 45 mA 500 mA Protection class 2
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree	+/- 10% 24 VDC 45 mA 500 mA Protection class 2
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree OPTICAL DATA	+/- 10% 24 VDC 45 mA 500 mA Protection class 2 3
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree OPTICAL DATA Light source	+/- 10% 24 VDC 45 mA 500 mA Protection class 2 3 LED
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree OPTICAL DATA Light source Light colour	+/- 10% 24 VDC 45 mA 500 mA Protection class 2 3 LED Red
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree OPTICAL DATA Light source Light colour Optical signal image	+/- 10% 24 VDC 45 mA 500 mA Protection class 2 3 LED Red Permanent
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree OPTICAL DATA Light source Light colour Optical signal image Service life optical	+/- 10% 24 VDC 45 mA 500 mA Protection class 2 3 LED Red Permanent
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree OPTICAL DATA Light source Light colour Optical signal image Service life optical APPROVAL DATA	+/- 10% 24 VDC 45 mA 500 mA Protection class 2 3 LED Red Permanent 100,000 h maximum


For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.

i



Mini free-standing Beacons / LED-Permanent Light 204 LED Perm. Beacon WM 24VAC/DC RD

Conforms with ATEX-directive	No
Conforms with CCC	No
Conforms with UL	CULus
UL Type Rating	Type 12
Conforms with FCC	No
Conforms with IC	No
EAC certificate available	Yes
Conforms with AS-I	No
ICAO Certification	No
Conforms with DNV	No
Conforms with RoHS CN	No
Conforms with VdS	No



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.