

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [15-31-1032](#)  
**Status:** **Active**  
**Description:** 4.80mm Pitch Wire-to-Wire Receptacle Housing, 3 Circuits

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-5025-003 (PDF)</a>
<a href="#">Product Specification PS-5025-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-5025-002 (PDF)</a>	

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">5025</a>
Application	Power, Wire-to-Wire
Product Name	N/A
UPC	800753622111

**Physical**

Circuits (maximum)	3
Flammability	94V-2
Gender	Female
Glow-Wire Compliant	No
Net Weight	1550.800/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.80mm
Pitch - Termination Interface	4.80mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +105°C

**Material Info**

Old Part Number	5025-03R1
-----------------	-----------

**Reference - Drawing Numbers**

Product Specification	PS-5025-001, PS-5025-002, PS-5025-003, RPS-5025-004
Sales Drawing	SD-5025-03R1

**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

**Contains SVHC: No**

**Low-Halogen Status**

**Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

[5025Series](#)

**Mates With**

[5025 Plug](#)

**Use With**

[5005](#)