



Optional nozzles for Quick850 series

Unit : mm


• Nozzles

NOTE


The size in Name/Specifications indicates the size of IC package.




A1125
QFP 10 × 10




A1126
QFP 14 × 14




A1127
QFP 17.5 × 17.5




A1128
QFP 14 × 20




A1129
QFP 28 × 28




A1135
PLCC 17.5 × 17.5
(44pins)




A1136
PLCC 20 × 20
(52pins)




A1137
PLCC 25 × 25
(68pins)




A1138
PLCC 30 × 30
(84pins)




A1139
PLCC 12.5 × 7.3
(18pins)




A1140
PLCC 11.5 × 11.5
(28pins)




A1141
PLCC 17.5 × 14
(32pins)




A1180
BQFP 17 × 17




A1181
BQFP 19 × 19




A1182
BQFP 24 × 24




A1184
SOJ 18 × 8




A1185
TSOL 13 × 10




A1186
TSOL 18 × 10




A1187
TSOL 18.5 × 8




A1188
PLCC 9 × 9
(20pins)




A1189
PLCC 34 × 34
(100pins)




A1203
QFP 35 × 35




A1214
SOJ 10 × 26




A1215
QFP 42.5 × 42.5




A1257
SOP11 × 21




A1258
SOP 7.6 × 12.7




A1259
SOP 13 × 28




A1260
SOP 8.6 × 18




A1261
QFP 20 × 20




A1262
QFP 12 × 12




A1263
QFP 28 × 40



A1264
QFP 40 × 40



A1265
QFP 32 × 32




A1124
Single $\phi 2.5$




A1130
Single $\phi 4.4$




A1131
SOP 4.4 × 10




A1132
SOP 5.6 × 13




A1133
SOP 7.5 × 15




A1134
SOP 7.5 × 18



A1142
Bent Single 1.5 × 3



A1183
SOJ 15 × 8



A1325 Dual Single $\phi 1.5 \times 5 - 10$
Adjustable Pitch

