


# MA 2,5/5 - 0 to 4 mm<sup>2</sup> (22 to 12 AWG), 30 Amps, 5 mm

MA 2,5/5

MA 2,5/5.P

Spacing 5 mm (.200")

Spacing 5 mm (.200")




Terminal block for ground wire

Standard 5 mm block

[View correct mounting of ground block on rail](#)

		Type	P/N	
Standard blocks	Grey body	MA 2,5/5	115 486.03	
	Blue body	MA 2,5/5.N	125 486.05	
	Yellow body	--	--	
	Orange body	--	--	
	Green body	--	--	
	Red body	--	--	
	Black body	--	--	
Terminal blocks for ground wires	Green / yellow body (with rail contact)	MA 2,5/5.P	165 488.27	
	Yellow+green body (without rail contact)	--	--	
<b>Characteristics</b>		<b>DIN-VDE</b>	<b>UL</b>	<b>CSA</b>
Wire size mm <sup>2</sup> / AWG	Solid wire	0-4	22-12 AWG	22-12 AWG
	Stranded wire	0-2.5		
Rated voltage	V AC / = DC	750/900 Gr.C	600	600
Rated current	A	26	30	25
Rated wire size	mm <sup>2</sup> / AWG	2.5 mm <sup>2</sup>	12 AWG	12 AWG
Wire stripping length	mm / inches	10 mm / .39"		
Recommended torque	Nm / lb.in	0.4-0.6 Nm / 3.5-5.3 lb-in		

Accessories		Type	P/N		
	End stop (all rails)	BAM	th. 9.1	103 002.26	
	End section	grey	FEM6	*th. 2.8	118 368.16
		blue	FEM6	*th. 2.8	128 368.10
		yellow	FEM6	th. 2.8	103 062.21
		orange	FEM6	*th. 2.8	103 126.16
		green	FEM6	*th. 2.8	103 125.15



Circuit separator	grey	SCMA5	*	116 728.25
Separator end section (block)	grey	SCF6	*th. 3	118 707.03
Separator end section (rail)	grey	SCFM6	th. 3	114 825.05
Test socket	DIA. 2 mm	AL2 (1)	*	163 046.24
	DIA. 3 mm	--	--	--
	DIA. 4 mm	--	--	--
Test device		DCB	*blue	105 028.21
Test plug	DIA. 2 mm	FC2	*DIA. 2	007 865.26
Preassembled jumper bar IP20 touchproof (see Accessories section)	2 poles	BJM5 (1)	*	176 273.01
	3 poles	BJM5 (1)	*	176 274.02
	4 poles	BJM5 (1)	*	176 275.03
	5 poles	BJM5 (1)	*	176 276.04
	10 poles	BJM5 (1)	*	176 277.05
Connector plate		--	--	--
Jumper bar not preassembled Post + screw + washer		BJS5 (1)	*20 poles	177 652.06
		EV5	*	168 629.16
Comb-type jumper bar Isolating cover	10 poles	PC5	*	113 544.12
		EIP	*	113 550.24
Shielding connector		CBM5	*th. 0.5	178 745.14
		CBM8	*th. 0.8	178 746.15
Protection label	3 blocks	--	--	--
Screw for protection label	4 blocks	--	--	--
		--	--	--
Markers (see Accessories section)		RC510 Side and Top		