

# CRIMPFOX 4 IN 1 - Multi-function tool



1200101

<https://www.phoenixcontact.com/us/products/1200101>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Tool for processing ferrules according to DIN 46228-4, 0.5 mm<sup>2</sup> to 2.5 mm<sup>2</sup>, equipped with pressure lock, magazine, cutting, stripping, twisting, and crimping unit.

## Your advantages

- Robust and durable due to use of resistant plastics and annealed metals
- Multifunctional crimping pliers for the processing of Taped ferrules according to DIN 46228-4
- Integrated pressure lock ensures consistently high-quality crimping
- Up to 30% time savings since the process steps required for assembling conductors can be carried out using only one tool
- Visualized process flows directly on the pliers simplify operation

## Commercial Data

Item number	1200101
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	BH31
Product Key	BH3131
Catalog Page	Page 415 (C-3-2019)
GTIN	4055626042381
Weight per Piece (including packing)	329 g
Weight per Piece (excluding packing)	286.3 g
Customs tariff number	82032000
Country of origin	DE

# CRIMPFOX 4 IN 1 - Multi-function tool



1200101

<https://www.phoenixcontact.com/us/products/1200101>

## Technical Data

### Notes

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Product properties

Product type	Crimping tool
Compression	Indent crimp
Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	2.5 mm <sup>2</sup>
AWG min	20
AWG max	14

### Connection data

#### Conductor connection

Cross section range, metric	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Cross section range AWG	20 ... 14
Stripping length	11 mm

### Dimensions

Width	31.5 mm
Height	100 mm
Length	180 mm

### Material specifications

Color	black
-------	-------

# CRIMPFOX 4 IN 1 - Multi-function tool



1200101

<https://www.phoenixcontact.com/us/products/1200101>

## Approvals



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX 4 IN 1 - Multi-function tool



1200101

<https://www.phoenixcontact.com/us/products/1200101>

## Classifications

### ECLASS

ECLASS-11.0	21043811
ECLASS-12.0	21043811
ECLASS-13.0	21043811

### ETIM

ETIM 8.0	EC000168
----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX 4 IN 1 - Multi-function tool



1200101


<https://www.phoenixcontact.com/us/products/1200101>

## Accessories

### AI 0,5-8 WH S1 - Ferrule

1200104

<https://www.phoenixcontact.com/us/products/1200104>




Taped ferrules, 0.5 mm<sup>2</sup>, sleeve length 8 mm, with plastic collar, according to DIN 46228-4, white, for processing with the CRIMPFOX 4 IN 1, 10 strips each with 50 sleeves per strip.

---

### AI 0,75- 8 GY S1 - Ferrule

1200105

<https://www.phoenixcontact.com/us/products/1200105>



Taped ferrules, 0.75 mm<sup>2</sup>, sleeve length 8 mm, with plastic collar, according to DIN 46228-4, gray, for processing with the CRIMPFOX 4 IN 1, 10 strips each with 50 sleeves per strip.

# CRIMPFOX 4 IN 1 - Multi-function tool


1200101

<https://www.phoenixcontact.com/us/products/1200101>

## AI 1,0-8 RD S1 - Ferrule

1200106

<https://www.phoenixcontact.com/us/products/1200106>



Taped ferrules, 1.0 mm<sup>2</sup>, sleeve length 8 mm, with plastic collar, according to DIN 46228-4, red, for processing with the CRIMPFOX 4 IN 1, 10 strips each with 50 sleeves per strip.

---

## AI 1,5-8 BK S1 - Ferrule

1200107

<https://www.phoenixcontact.com/us/products/1200107>



Taped ferrules, 1.5 mm<sup>2</sup>, sleeve length 8 mm, with plastic collar, according to DIN 46228-4, black, for processing with the CRIMPFOX 4 IN 1, 10 strips each with 50 sleeves per strip.

# CRIMPFOX 4 IN 1 - Multi-function tool


1200101

<https://www.phoenixcontact.com/us/products/1200101>

## AI 2,5-8 BU S1 - Ferrule

1200108

<https://www.phoenixcontact.com/us/products/1200108>




Taped ferrules, 2.5 mm<sup>2</sup>, sleeve length 8 mm, with plastic collar, according to DIN 46228-4, blue, for processing with the CRIMPFOX 4 IN 1, 10 strips each with 40 sleeves per strip.

---

## AI 0,75- 8 BU S1 - Ferrule

1200163

<https://www.phoenixcontact.com/us/products/1200163>



Ferrule, Dimensions according to DIN 46228-4, with color-coded plastic collars according to NF C 63-023:1994-02, for processing with the CRIMPFOX 4 in 1, sleeve length: 8 mm, length: 14 mm, color: blue, number of strips: 10, number of sleeves per strip: 50

# CRIMPFOX 4 IN 1 - Multi-function tool




1200101

<https://www.phoenixcontact.com/us/products/1200101>

## AI 2,5-8 GY S1 - Ferrule

1200164

<https://www.phoenixcontact.com/us/products/1200164>



Ferrule, Dimensions according to DIN 46228-4, with color-coded plastic collars according to NF C 63-023:1994-02, for processing with the CRIMPFOX 4 in 1, sleeve length: 8 mm, length: 14 mm, color: gray, number of strips: 10, number of sleeves per strip: 40

---

## CRIMPFOX 4 IN 1/MAG - Magazine

1200103

<https://www.phoenixcontact.com/us/products/1200103>



Ferrule magazine for CRIMPFOX 4 IN 1, for ferrules with insulating collars from 0.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, with a length of 8 mm

---

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)