


Alphabetical Picture Part Number
SEARCH SEARCH SEARCH

Go To Step Search™ Screen

280360 -- 1 of 1 products

AMPMODU
Locking Clip, Mod. IV and Short Point Products

General **INFO**
 Sales **INFO**
 Customer Drawings **SPECIFICATIONS**



Line art represents typical product only.

Searchable Features:

# of Positions	6
# of Rows	Single
Centerline Spacing	.100 [2.54] in. [mm]
Housing Configuration	Both Ends Closed
Contact Type	Mod II
Mating Polarization	No
Mating Connector Lock	With
Strain Relief	Without
Keyed	No

Other Properties:

Dim. A	.681 [17.30] in. [mm]
Dim. B	.500 [12.70] in. [mm]
Dim. C	.620 [15.75] in. [mm]
Mating Connector Lock Type	Detent
Housing Material	Thermoplastic
Housing Flammability Rating	UL 94V-1
Housing Color	Black