

## ASSMANN VGA Monitor connection cable, HD15/M - HD15/M

AK-310103-050-S  
EAN 4016032344896



**VGA Monitor connection cable, HD15 M/M, 5.0m, 3Coax/7C, 2xferrite, bl**

For connection of a PC, for example, with a monitor or beamer /projector.

**Offers high-quality protection against external interferences and prevents ghost images and other image faults.**

- Support 1280 x 1024 pixel with 60Hz
- Connector 1: HD DSUB, 15-pin, plug
- Connector 2: HD DSUB, 15-pin, plug
- Cable type: 3Coax + 7-wire
- Display Data Channel: DDC2

- Hoods: molded
- Shielding: Double shielding
- AWG: 28
- Wire material: CU
- Connector surface: nickel-plated
- Ferrite filter: 2 x ferrite beads
- Color cable: black
- Color connector: black
- Length: 5 m
- Packaging: Polybag
- Assortment: VGA Cables

Logistische Daten						
	Anzahl (Stück)	Gewicht (kg)	Tiefe (cm)	Breite (cm)	Höhe (cm)	cm <sup>3</sup>
Karton-VPE	20	10,50	38,00	32,00	28,00	34.048,00
Innen-VPE	5	2,63	21,00	26,00	10,00	5.460,00
Einzel-VPE	1	0,53	18,00	18,00	5,50	1.782,00
Netto einzeln ohne VP	1	0,50	16,50	16,50	4,50	1.225,12



Weitere Anwendungsbilder:

