



ENGLISH

Datasheet

RS Pro Amalgamating tape 19mm x 10m

RS Stock No **1469000**

A non-adhesive, polythene, self-amalgamating tape, which can be applied easily, with an easily removed interleave.

- Easy unwind
- Extremely flexible
- Excellent conformability to awkward shapes
- Water resistant
- Ozone resistant
- UV resistant
- Excellent low and high temperature performance
- Strong
- Resistant to chemicals; including alkalis, hydraulic fluids and vegetable oils
- High dielectric strength



Technical Details

Thickness	0.50mm
Breaking Load	12.0 N/cm
Elongation	600%
Electrical Strength	34 kV/mm
Operating Temperature	-35°C to +130°C
RoHS Compliant	Yes
Storage Temperature	+12°C to +25°C
Application Temperature	0°C to +40°C

STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.