







МИНИАТЮРНЫЕ ЛАМПЫ НАКАЛИВАНИЯ

СИСТЕМА ОБОЗНАЧЕНИЙ: **H26 - XXX XXX**
 1 2 3



1. Серия
2. Напряжение (025 = 2.5 В; 06 = 6 В)
3. Ток (05 = 0.5 А; 0125 = 0.125 А)

МИНИАТЮРНЫЕ ЛАМПЫ НАКАЛИВАНИЯ


<p>Серия Н1</p>  <p>2.5В, 6В, 6.3В, 12В, 24В, 60В, 110В 0.12 Вт - 4.8 Вт</p>	<p>Серия Н3</p>  <p>2В, 2.5В, 3.5В, 4.8В, 6В, 9В, 12В, 24В, 60В 0.12 Вт - 4.8 Вт</p>	<p>Серия Н5</p>  <p>2.5В, 6В, 12В, 24В, 60В, 110В 0.12 Вт - 4.8 Вт</p>	<p>Серия Н10</p>  <p>1.5В, 2.5В, 3.5В, 6В, 12В, 14В, 24В 0.3 Вт - 4.8 Вт</p>	<p>Серия Н12</p>  <p>2В, 2.5В, 6.2В, 12В, 14В, 24В, 60В, 90В, 110В 0.12 Вт - 4.8 Вт</p>	<p>Серия Н37</p>  <p>3В, 6В, 12В, 24В 0.3Вт-1.4Вт</p>	<p>Серия Н14</p>  <p>2.5В 0.24 Вт - 1.11 Вт</p>
<p>Серия Н19</p>  <p>2.5В, 3В, 3.5В, 4.5В, 6В, 12В, 24В 0.15 Вт - 2.4 Вт</p>	<p>Серия Н20</p>  <p>6В, 12В 0.25 Вт - 3 Вт</p>	<p>Серия Н21</p>  <p>6В, 12В 0.25 Вт - 3 Вт</p>	<p>Серия Н22</p>  <p>6В, 12В 0.25 Вт - 3 Вт</p>	<p>Серия Н26</p>  <p>2.5В, 3.8В, 6В 0.6 Вт - 3 Вт</p>	<p>Серия Н28</p>  <p>2.5В, 3.8В, 6В 0.6 Вт - 3 Вт</p>	<p>Серия Н61</p>  <p>12В, 24В, 60В, 110В 1.9 Вт - 3 Вт</p>

МИНИАТЮРНЫЕ ЛАМПЫ С ФЛАНЦЕВЫМ ЦОКОЛЕМ



ДВУХЦОКОЛЬНЫЕ ЛАМПЫ

<p>Серия Н17</p>  <p>2.5В, 3.6В, 4.8В, 6В, 7.2В 0.62 Вт - 3.6 Вт</p>	<p>Серия Н36</p>  <p>3В, 6В, 12В, 24В 0.3 Вт - 1.4 Вт</p>	<p>Серия Н49</p>  <p>3В, 6В, 9В, 12В 1 Вт - 3 Вт</p>	<p>Серия Н53</p>  <p>12В 5 Вт - 10 Вт</p>
--	---	--	---













МИНИАТЮРНЫЕ ЛАМПЫ С БАЙОНЕТНЫМ ЦОКОЛЕМ

<p>Серия Н2</p>  <p>2.5В, 6.3В, 12В, 24В, 60В, 110В 0.12 Вт - 4.8 Вт</p>	<p>Серия Н4</p>  <p>2.5В, 3.5В, 6В, 9В, 12В, 24В, 60В 0.12 Вт - 4.8 Вт</p>	<p>Серия Н6</p>  <p>2.5В, 3.5 В, 6В, 12В, 24В, 60В 0.12 Вт - 4.8 Вт</p>	<p>Серия Н11</p>  <p>2.5В, 6.3В, 12В, 24В, 60В 0.75 Вт - 6 Вт</p>	<p>Серия Н13</p>  <p>2.5В, 6В, 12В, 24В, 60В, 110В 0.24 Вт - 6 Вт</p>	<p>Серия Н27</p>  <p>2.5В, 3.8В, 6В 0.6 Вт - 3 Вт</p>	<p>Серия Н30</p>  <p>6В, 12В, 24В 3 Вт - 10 Вт</p>
--	--	---	---	---	--	--

МИНИАТЮРНЫЕ ЛАМПЫ БЕСЦОКОЛЬНЫЕ (С ПРОВОЛОЧНЫМИ ВЫВОДАМИ)

<p>Серия Н33</p>  <p>2.5В, 3В, 4.5В, 6В 0.15 Вт - 0.6 Вт</p>	<p>Серия Н34</p>  <p>2.5В, 3В, 4.5В, 6В 0.15 Вт - 0.6 Вт</p>	<p>Серия Н35</p>  <p>1.5В, 2.5В, 3В, 3.5В, 4.5В, 6В 0.15 Вт - 0.6 Вт</p>	<p>Серия Н39 для автомагнитол</p>  <p>2.5В, 3В, 6В, 9В, 12В, 14В 0.25 Вт - 0.7 Вт</p>	<p>Серия Н40</p>  <p>2.5В, 3В, 6В, 9В, 12В, 24В 0.25 Вт - 1.4 Вт</p>	<p>Серия Н41</p>  <p>3В, 6В, 9В, 12В, 24В 0.3 Вт - 1.4 Вт</p>
--	--	--	---	---	---

ДЕРЖАТЕЛИ ЛАМП

 <p>E10H3</p>	 <p>E10H5</p>	 <p>E10H6</p>	 <p>E10H7</p>	 <p>E10H8</p>	 <p>E10H10</p>	 <p>BA9SH2</p>	 <p>BA9SH3</p>	 <p>E5H3</p>	 <p>E5H4</p>	 <p>E5H1</p>	 <p>E5H2</p>
--	---	---	---	---	--	--	--	--	---	--	--