


THA.209.A1A

TeeBox 7mm to 14mm cable max IP68 rated Screw fixing 4 cable entries 16A



SPECIFICATION

Cable Entries	4
Body Material	PA66 / SEBS/ TPE
Max Current (A)	16
Minimum Temp Rating °C	-40
IP Rating	68
Max Temp Rating °C	125
Comments	Photo is representative of product, see line drawing
Fixing System	Screw
Maximum Cable Diameter (mm)	14
Minimum Cable Diameter (mm)	7
Temperature "T" Rating	T85