



Han® PushPull,  
type acc. to IEC 61076-3-117 variant 14  
Housing bulkhead mounting and housing cable-to-cable combinations

Identification	Part number	Drawing	Dimensions in mm
<b>RJ45 female inserts</b> <span style="float: right;">②</span>  Cat. 5, 4 poles, 10/100 Mbit/s IDC for AWG 24-22 solid and stranded  Cat. 6 <sub>A</sub> , 8 poles, 10/100 Mbit/s and 1/10 Gbit/s IDC for AWG 28-24 solid and stranded  Cat. 6 <sub>A</sub> , 8 poles, 10/100 Mbit/s and 1/10 Gbit/s IDC for AWG 24-22 solid and stranded  Cat. 6 <sub>A</sub> , 8 poles, 10/100 Mbit/s and 1/10 Gbit/s preLink® IDC for AWG 23/22 solid and stranded  Cat. 6 <sub>A</sub> , 8 poles, 10/100 Mbit/s and 1/10 Gbit/s preLink® IDC for AWG 27/26 solid and stranded  Cat. 6 <sub>A</sub> , 8 poles, 10/100 Mbit/s and 1/10 Gbit/s preLink® IDC for AWG 23/22 or AWG 27/26 depending on the separately orderable preLink® terminal module (20 82 000 0001 / 20 82 000 0003)  Cat. 6, 8 poles, 10/100 Mbit/s and 1/10 Gbit/s RJ45 system cable jack on connector	   09 45 545 1120  09 45 545 1561  09 45 545 1562  20 82 001 0001  20 82 001 0002  20 82 000 0002  0.15 m up to 10.0 m 09 45 545 1500 09 45 545 1518		   13,15  15,6
<b>Han® PushPull Housing cable-to-cable</b> <span style="float: right;">③</span>  plastic, black (not in combination with Housing bulkhead mounting 09 35 012 0312!)  for cable outer diameter 6.5 ... 9.5 mm  for cable outer diameter 9 ... 13 mm	   09 35 002 0431  09 35 002 0433	2X REMFORM $\phi 3 \times 8$ TORX screws  	   70 54,5 22,4