

Sample set - SAMPLE DMC 0,5/ 4-G1-2,54 THR - 1859518

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)

Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 4, Pitch: 2.54 mm, Color: black, Contact surface: Gold, Mounting: THR soldering



The figure shows a 10-pos. version with 20 contacts













Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	4 055626 111919
Weight per Piece (excluding packing)	1.9 g
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length	9.64 mm
Pitch	2.54 mm
Dimension a	7.62 mm
Width	10.66 mm
Height	7.39 mm
Length of the solder pin	2 mm
Pin dimensions	0,64 x 0,64 mm
Pin spacing	2.54 mm
Hole diameter	1.2 mm

General

Range of articles	DMC 0,5/G1-THR
Insulating material group	Illa
Rated surge voltage (III/3)	2.5 kV



Sample set - SAMPLE DMC 0,5/ 4-G1-2,54 THR - 1859518

Technical data

General

Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	32 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	160 V
Connection in acc. with standard	EN-VDE
Nominal current I _N	6 A
Insulating material	LCP
Flammability rating according to UL 94	V0
Color	black
Number of positions	4

Standards and Regulations

Connection in acc. with standard	EN-VDE
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

ETIM

ETIM 5.0	EC002637

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC



Sample set - SAMPLE DMC 0,5/ 4-G1-2,54 THR - 1859518

Accessories

Accessories

Labeled terminal marker

Marker card - SK 2,54/2,8:FORTL.ZAHLEN - 0804853



Marker card, Card, white, labeled, Horizontal: Consecutive numbers 1 - 10, 11 - 20, etc. up to 91 - 99, Mounting type: Adhesive, for terminal block width: 2.54 mm, Lettering field: 2.54 x 2.8 mm

Additional products


Printed-circuit board connector - DFMC 0,5/ 4-ST-2,54 - 1844594




Plug, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 4 with 8 contacts, pitch: 2.54 mm, connection method: spring connection, color: black, contact surface: gold

Drawings





Dimensional drawing



Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com