

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet ✓RoHS₃ **tasker® C114 – 2x0,25 mm²** **Low Capacity Balanced Microphone Cable**



A	B	C	D	E
---	---	---	---	---

CATEGORY Balanced Microphone Cable (See Audio Catalogue)
APPLICATIONS Pre Made Audio Cables and Microphones.

- A:** PVC Sheath. Available in different color .
Outer cable Diam. Ø 6,00 (±0,20) mm.
- B:** Shielding O.F.C. red copper Spiral covering 100%.
- C:** The cores are stranded in a pair with textile waste filler between conductors and wrapped with not woven polyester based tape.
- D:** Core Insulation with a compact PE, colored one Orange and one Transparent. Diam. Ø 1,50 (±0,20) mm.
- E:** O.F.C. red copper, formation 8x0,20 mm.
Nom. Cross section 2x0,25 mm².

MARKING **tasker®** C 114 2x0.25 – 23 AWG O.F.C. Low Capacitance Flex Microphone Cable
 Made in Italy

CUSTOM PRODUCTION This product may be custom produced also in **L.S.Z.H.** polymer, **PE, PUR,** or Metallic Armored.

Cable Properties

Conductor Resistance	75 Ω/Km
Capacity Core/Core	55 pF/mt
Capacity Core/Shield	90 pF/mt
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego		Outdoor Limited	Esterno Limitato	Posa	X	Restricted Mobile	Mobile Limitata	Informazioni	X	Ver. A / 16.05.16
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			