


C TYPE



Specifications:

Contact Resistance: $30\text{m}\Omega$ max.at DC 100 mA
 Insulator Resistance: $1000\text{M}\Omega$ min.at DC 500V
 Current Rating: 1 AMP

Dielectric Withstanding

Voltage: AC 500V For 1 minute
 Operating Temperature: -55°C -- $+105^{\circ}\text{C}$
 Contact: Phosphor bronze
 Housing: PBT &30% Glass Fiber(UL 94V-0)

设计/Designed by	绘图/Drawng by	审核/Checked by	批准/Approved by	未注公差 General Tolerance	
		图名/Title	文件编号/File No.	x. ±0.2	x.' ±2'
		116-CG1	QJ/XYT-12043	.x ±0.1	.x' ±1'
		备注/Remark	页序/Sheet	.xx ±0.05	.xx' ±0.5
				.xxx ±0.01	
			单位/Units:	mm	

序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date
-----------	--------------------	--------------	---------