

Thick Film Chip Resistor 0603

multicomp^{PRO}




Features

- Small size and light weight
- Suitable for both wave and reflow soldering
- Reduction of assembly costs

Performance Specification

Temperature Coefficient	: 1Ω to 10Ω ±400PPM/°C 11Ω to 100Ω ±200PPM/°C >100Ω ±100PPM/°C
Short Time Overload	: ±5% : ±(2% +0.1Ω)Max. ±1% : ±(1% +0.1Ω)Max.
Insulation Resistance	: Min. 1,000MΩ
Dielectric Withstanding Voltage	: No evidence of flashover, mechanical damage, arcing or insulation breakdown.
Terminal Bending	: ±(1% +0.05Ω) Max.
Soldering Heat	: ±(1% +0.05Ω) Max.
Solderability	: Min. 95% coverage
Temperature Cycling	: ±5% : ±(1% +0.05Ω) Max. ±1% : ±(0.5% +0.05Ω) Max.
Humidity (Steady State)	: ±5% : ±(3% +0.1Ω) Max. ±1% : ±(0.5% +0.1Ω) Max.
Load Life in Humidity	: ±5% : ±(3% +0.1Ω) Max. ±1% : ±(1% +0.1Ω) Max.
Load Life	: ±5% : ±(3% +0.1Ω) Max. ±1% : ±(1% +0.1Ω) Max.


Derating Curve



Thick Film Chip Resistor 0603

multicomp PRO

Dimension



Type	Dimension (mm)				
	L	W	H	ℓ ₁	ℓ ₂
0603	1.6 ±0.1	0.8 ^{+0.15} / _{-0.1}	0.45 ±0.1	0.3 ±0.2	0.3 ±0.2

Type	Power Rating at 70°C	Max. Working Voltage	Max. Overload Voltage	Dielectric Withstanding Voltage	Tolerance %	Resistance Range
0603	1/10W-S 1/16W	1A	2A	-	Jumper	<50mΩ
		50V	100V	300V	±1%	10Ω to 1MΩ
					±2%	1Ω to 10MΩ
					±5%	1Ω to 10MΩ

Part Number Table

Description	Part Number	Description	Part Number
Thick Film Resistor, 0Ω, 0.063W	MC0603WG00000T5E-TC	Thick Film Resistor, 1.8Ω, 0.063W, 1%	MC0063W060311R80
Thick Film Resistor, 0Ω, 0.063W	MC0603WG00000T5E-TR	Thick Film Resistor, 1.87Ω, 0.063W, 1%	MC0063W060311R87
Thick Film Resistor, 0Ω, 0.063W	MC0063W06030R	Thick Film Resistor, 1.96Ω, 0.063W, 1%	MC0063W060311R96
Thick Film Resistor, 1Ω, 0.063W, 1%	MC0063W060311R0	Thick Film Resistor, 2Ω, 0.063W, 1%	MC0063W060312R0
Thick Film Resistor, 1.1Ω, 0.063W, 1%	MC0063W060311R10	Thick Film Resistor, 2.2Ω, 0.063W, 5%	MC0063W060352R2
Thick Film Resistor, 1.15Ω, 0.063W, 1%	MC0063W060311R15	Thick Film Resistor, 2.2Ω, 0.063W, 1%	MC0063W060312R2
Thick Film Resistor, 1.2Ω, 0.063W, 1%	MC0063W060311R20	Thick Film Resistor, 2.4Ω, 0.063W, 1%	MC0063W060312R40
Thick Film Resistor, 1.21Ω, 0.063W, 1%	MC0063W060311R21	Thick Film Resistor, 2.49Ω, 0.063W, 1%	MC0063W060312R49
Thick Film Resistor, 1.27Ω, 0.063W, 1%	MC0063W060311R27	Thick Film Resistor, 2.7Ω, 0.063W, 1%	MC0063W060312R70
Thick Film Resistor, 1.3Ω, 0.063W, 1%	MC0063W060311R30	Thick Film Resistor, 2.74Ω, 0.063W, 1%	MC0063W060312R74
Thick Film Resistor, 1.33Ω, 0.063W, 1%	MC0063W060311R33	Thick Film Resistor, 2.87Ω, 0.063W, 1%	MC0063W060312R87
Thick Film Resistor, 1.4Ω, 0.063W, 1%	MC0063W060311R40	Thick Film Resistor, 3Ω, 0.063W, 1%	MC0063W060313R0
Thick Film Resistor, 1.47Ω, 0.063W, 1%	MC0063W060311R47	Thick Film Resistor, 3.16Ω, 0.063W, 1%	MC0063W060313R16
Thick Film Resistor, 1.5Ω, 0.063W, 5%	MC0063W060351R5	Thick Film Resistor, 3.3Ω, 0.063W, 5%	MC0063W060353R3
Thick Film Resistor, 1.5Ω, 0.063W, 1%	MC0063W060311R5	Thick Film Resistor, 3.3Ω, 0.063W, 1%	MC0063W060313R3
Thick Film Resistor, 1.54Ω, 0.063W, 1%	MC0063W060311R54	Thick Film Resistor, 3.32Ω, 0.063W, 1%	MC0063W060313R32
Thick Film Resistor, 1.6Ω, 0.063W, 1%	MC0063W060311R60	Thick Film Resistor, 3.48Ω, 0.063W, 1%	MC0063W060313R48
Thick Film Resistor, 1.62Ω, 0.063W, 1%	MC0063W060311R62	Thick Film Resistor, 3.6Ω, 0.063W, 1%	MC0063W060313R60
Thick Film Resistor, 1.78Ω, 0.063W, 1%	MC0063W060311R78	Thick Film Resistor, 3.65Ω, 0.063W, 1%	MC0063W060313R65

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Thick Film Chip Resistor 0603

multicomp PRO

Description	Part Number
Thick Film Resistor, 3.83Ω, 0.063W, 1%	MC0063W060313R83
Thick Film Resistor, 3.9Ω, 0.063W, 1%	MC0063W060313R90
Thick Film Resistor, 4.22Ω, 0.063W, 1%	MC0063W060314R22
Thick Film Resistor, 4.3Ω, 0.063W, 1%	MC0063W060314R30
Thick Film Resistor, 4.42Ω, 0.063W, 1%	MC0063W060314R42
Thick Film Resistor, 4.64Ω, 0.063W, 1%	MC0063W060314R64
Thick Film Resistor, 4.7Ω, 0.063W, 5%	MC0063W060354R7
Thick Film Resistor, 4.7Ω, 0.063W, 1%	MC0063W060314R7
Thick Film Resistor, 4.87Ω, 0.063W, 1%	MC0063W060314R87
Thick Film Resistor, 5.1Ω, 0.063W, 1%	MC0063W060315R10
Thick Film Resistor, 5.11Ω, 0.063W, 1%	MC0063W060315R11
Thick Film Resistor, 5.6Ω, 0.063W, 1%	MC0063W060315R60
Thick Film Resistor, 5.62Ω, 0.063W, 1%	MC0063W060315R62
Thick Film Resistor, 5.9Ω, 0.063W, 1%	MC0063W060315R90
Thick Film Resistor, 6.19Ω, 0.063W, 1%	MC0063W060316R19
Thick Film Resistor, 6.2Ω, 0.063W, 1%	MC0063W060316R20
Thick Film Resistor, 6.49Ω, 0.063W, 1%	MC0063W060316R49
Thick Film Resistor, 6.8Ω, 0.063W, 5%	MC0063W060356R8
Thick Film Resistor, 6.8Ω, 0.063W, 1%	MC0063W060316R8
Thick Film Resistor, 6.81Ω, 0.063W, 1%	MC0063W060316R81
Thick Film Resistor, 7.15Ω, 0.063W, 1%	MC0063W060317R15
Thick Film Resistor, 7.5Ω, 0.063W, 1%	MC0063W060317R50
Thick Film Resistor, 7.87Ω, 0.063W, 1%	MC0063W060317R87
Thick Film Resistor, 8.2Ω, 0.063W, 1%	MC0063W060318R20
Thick Film Resistor, 8.25Ω, 0.063W, 1%	MC0063W060318R25
Thick Film Resistor, 8.66Ω, 0.063W, 1%	MC0063W060318R66
Thick Film Resistor, 9.1Ω, 0.063W, 1%	MC0063W060319R10
Thick Film Resistor, 9.53Ω, 0.063W, 1%	MC0063W060319R53
Thick Film Resistor, 10Ω, 0.063W, 1%	MC0063W0603510R
Thick Film Resistor, 10Ω, 0.063W, 1%	MC0063W0603110R
Thick Film Resistor, 10.2Ω, 0.063W, 1%	MC0063W0603110R2
Thick Film Resistor, 10.5Ω, 0.063W, 1%	MC0063W0603110R5
Thick Film Resistor, 11Ω, 0.063W, 1%	MC0063W0603111R
Thick Film Resistor, 11.5Ω, 0.063W, 1%	MC0063W0603111R5
Thick Film Resistor, 12Ω, 0.063W, 5%	MC0063W0603512R
Thick Film Resistor, 12Ω, 0.063W, 1%	MC0063W0603112R
Thick Film Resistor, 12.1Ω, 0.063W, 1%	MC0063W0603112R1
Thick Film Resistor, 12.4Ω, 0.063W, 1%	MC0063W0603112R4
Thick Film Resistor, 12.7Ω, 0.063W, 1%	MC0063W0603112R7
Thick Film Resistor, 13Ω, 0.063W, 1%	MC0063W0603113R
Thick Film Resistor, 13.3Ω, 0.063W, 1%	MC0063W0603113R3

Description	Part Number
Thick Film Resistor, 14Ω, 0.063W, 1%	MC0063W0603114R
Thick Film Resistor, 14.3Ω, 0.063W, 1%	MC0063W0603114R3
Thick Film Resistor, 14.7Ω, 0.063W, 1%	MC0063W0603114R7
Thick Film Resistor, 15Ω, 0.063W, 5%	MC0063W0603515R
Thick Film Resistor, 15Ω, 0.063W, 1%	MC0063W0603115R
Thick Film Resistor, 15.4Ω, 0.063W, 1%	MC0063W0603115R4
Thick Film Resistor, 16Ω, 0.063W, 1%	MC0063W0603116R
Thick Film Resistor, 16.2Ω, 0.063W, 1%	MC0063W0603116R2
Thick Film Resistor, 16.5Ω, 0.063W, 1%	MC0063W0603116R5
Thick Film Resistor, 16.9Ω, 0.063W, 1%	MC0063W0603116R9
Thick Film Resistor, 17.8Ω, 0.063W, 1%	MC0063W0603117R8
Thick Film Resistor, 18Ω, 0.063W, 5%	MC0063W0603518R
Thick Film Resistor, 18Ω, 0.063W, 1%	MC0063W0603118R
Thick Film Resistor, 18.2Ω, 0.063W, 1%	MC0063W0603118R2
Thick Film Resistor, 18.7Ω, 0.063W, 1%	MC0063W0603118R7
Thick Film Resistor, 19.1Ω, 0.063W, 1%	MC0063W0603119R1
Thick Film Resistor, 19.6Ω, 0.063W, 1%	MC0063W0603119R6
Thick Film Resistor, 20Ω, 0.063W, 1%	MC0063W0603120R
Thick Film Resistor, 20.5Ω, 0.063W, 1%	MC0063W0603120R5
Thick Film Resistor, 21Ω, 0.063W, 1%	MC0063W0603121R
Thick Film Resistor, 21.5Ω, 0.063W, 1%	MC0063W0603121R5
Thick Film Resistor, 22Ω, 0.063W, 1%	MC0063W0603522R
Thick Film Resistor, 22Ω, 0.063W, 1%	MC0063W0603122R
Thick Film Resistor, 22.1Ω, 0.063W, 1%	MC0063W0603122R1
Thick Film Resistor, 22.6Ω, 0.063W, 1%	MC0063W0603122R6
Thick Film Resistor, 23.2Ω, 0.063W, 1%	MC0063W0603123R2
Thick Film Resistor, 23.7Ω, 0.063W, 1%	MC0063W0603123R7
Thick Film Resistor, 24Ω, 0.063W, 1%	MC0063W0603124R
Thick Film Resistor, 24.3Ω, 0.063W, 1%	MC0063W0603124R3
Thick Film Resistor, 24.9Ω, 0.063W, 1%	MC0063W0603124R9
Thick Film Resistor, 25.5Ω, 0.063W, 1%	MC0063W0603125R5
Thick Film Resistor, 26.1Ω, 0.063W, 1%	MC0063W0603126R1
Thick Film Resistor, 26.7Ω, 0.063W, 1%	MC0063W0603126R7
Thick Film Resistor, 27Ω, 0.063W, 5%	MC0063W0603527R
Thick Film Resistor, 27Ω, 0.063W, 1%	MC0063W0603127R
Thick Film Resistor, 27.4Ω, 0.063W, 1%	MC0063W0603127R4
Thick Film Resistor, 28Ω, 0.063W, 1%	MC0063W0603128R
Thick Film Resistor, 28.7Ω, 0.063W, 1%	MC0063W0603128R7
Thick Film Resistor, 30Ω, 0.063W, 1%	MC0063W0603130R
Thick Film Resistor, 30.1Ω, 0.063W, 1%	MC0063W0603130R1
Thick Film Resistor, 30.9Ω, 0.063W, 1%	MC0063W0603130R9

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Thick Film Chip Resistor 0603

multicomp PRO

Description	Part Number
Thick Film Resistor, 31.6Ω, 0.063W, 1%	MC0063W0603131R6
Thick Film Resistor, 33Ω, 0.063W, 5%	MC0063W0603533R
Thick Film Resistor, 33Ω, 0.063W, 1%	MC0063W0603133R
Thick Film Resistor, 33.2Ω, 0.063W, 1%	MC0063W0603133R2
Thick Film Resistor, 34Ω, 0.063W, 1%	MC0063W0603134R
Thick Film Resistor, 34.8Ω, 0.063W, 1%	MC0063W0603134R8
Thick Film Resistor, 35.7Ω, 0.063W, 1%	MC0063W0603135R7
Thick Film Resistor, 36Ω, 0.063W, 1%	MC0063W0603136R
Thick Film Resistor, 36.5Ω, 0.063W, 1%	MC0063W0603136R5
Thick Film Resistor, 37.4Ω, 0.063W, 1%	MC0063W0603137R4
Thick Film Resistor, 38.3Ω, 0.063W, 1%	MC0063W0603138R3
Thick Film Resistor, 39Ω, 0.063W, 5%	MC0063W0603539R
Thick Film Resistor, 39Ω, 0.063W, 1%	MC0063W0603139R
Thick Film Resistor, 39.2Ω, 0.063W, 1%	MC0063W0603139R2
Thick Film Resistor, 40.2Ω, 0.063W, 1%	MC0063W0603140R2
Thick Film Resistor, 41.2Ω, 0.063W, 1%	MC0063W0603141R2
Thick Film Resistor, 42.2Ω, 0.063W, 1%	MC0063W0603142R2
Thick Film Resistor, 43Ω, 0.063W, 1%	MC0063W0603143R
Thick Film Resistor, 43.2Ω, 0.063W, 1%	MC0063W0603143R2
Thick Film Resistor, 44.2Ω, 0.063W, 1%	MC0063W0603144R2
Thick Film Resistor, 45.3Ω, 0.063W, 1%	MC0063W0603145R3
Thick Film Resistor, 46.4Ω, 0.063W, 1%	MC0063W0603146R4
Thick Film Resistor, 47Ω, 0.063W, 5%	MC0063W0603547R
Thick Film Resistor, 47Ω, 0.063W, 1%	MC0063W0603147R
Thick Film Resistor, 47.5Ω, 0.063W, 1%	MC0063W0603147R5
Thick Film Resistor, 48.7Ω, 0.063W, 1%	MC0063W0603148R7
Thick Film Resistor, 49.9Ω, 0.063W, 1%	MC0063W0603149R9
Thick Film Resistor, 51Ω, 0.063W, 1%	MC0063W0603151R
Thick Film Resistor, 51.1Ω, 0.063W, 1%	MC0063W0603151R1
Thick Film Resistor, 52.3Ω, 0.063W, 1%	MC0063W0603152R3
Thick Film Resistor, 53.6Ω, 0.063W, 1%	MC0063W0603153R6
Thick Film Resistor, 54.9Ω, 0.063W, 1%	MC0063W0603154R9
Thick Film Resistor, 56Ω, 0.063W, 5%	MC0063W0603556R
Thick Film Resistor, 56Ω, 0.063W, 1%	MC0063W0603156R
Thick Film Resistor, 56.2Ω, 0.063W, 1%	MC0063W0603156R2
Thick Film Resistor, 57.6Ω, 0.063W, 1%	MC0063W0603157R6
Thick Film Resistor, 59Ω, 0.063W, 1%	MC0063W0603159R
Thick Film Resistor, 60.4Ω, 0.063W, 1%	MC0063W0603160R4
Thick Film Resistor, 61.9Ω, 0.063W, 1%	MC0063W0603161R9
Thick Film Resistor, 62Ω, 0.063W, 1%	MC0063W0603162R
Thick Film Resistor, 63.4Ω, 0.063W, 1%	MC0063W0603163R4

Description	Part Number
Thick Film Resistor, 64.9Ω, 0.063W, 1%	MC0063W0603164R9
Thick Film Resistor, 66.5Ω, 0.063W, 1%	MC0063W0603166R5
Thick Film Resistor, 68Ω, 0.063W, 5%	MC0063W0603568R
Thick Film Resistor, 68Ω, 0.063W, 1%	MC0063W0603168R
Thick Film Resistor, 68.1Ω, 0.063W, 1%	MC0063W0603168R1
Thick Film Resistor, 71.5Ω, 0.063W, 1%	MC0063W0603171R5
Thick Film Resistor, 73.2Ω, 0.063W, 1%	MC0063W0603173R2
Thick Film Resistor, 75Ω, 0.063W, 1%	MC0063W0603175R
Thick Film Resistor, 76.8Ω, 0.063W, 1%	MC0063W0603176R8
Thick Film Resistor, 78.7Ω, 0.063W, 1%	MC0063W0603178R7
Thick Film Resistor, 80.6Ω, 0.063W, 1%	MC0063W0603180R6
Thick Film Resistor, 82Ω, 0.063W, 5%	MC0063W0603582R
Thick Film Resistor, 82Ω, 0.063W, 1%	MC0063W0603182R
Thick Film Resistor, 82.5Ω, 0.063W, 1%	MC0063W0603182R5
Thick Film Resistor, 84.5Ω, 0.063W, 1%	MC0063W0603184R5
Thick Film Resistor, 86.6Ω, 0.063W, 1%	MC0063W0603186R6
Thick Film Resistor, 88.7Ω, 0.063W, 1%	MC0063W0603188R7
Thick Film Resistor, 90.9Ω, 0.063W, 1%	MC0063W0603190R9
Thick Film Resistor, 91Ω, 0.063W, 1%	MC0063W0603191R
Thick Film Resistor, 93.1Ω, 0.063W, 1%	MC0063W0603193R1
Thick Film Resistor, 95.3Ω, 0.063W, 1%	MC0063W0603195R3
Thick Film Resistor, 97.6Ω, 0.063W, 1%	MC0063W0603197R6
Thick Film Resistor, 100Ω, 0.063W, 1%	MC0063W06035100R
Thick Film Resistor, 100Ω, 0.063W, 1%	MC0063W06031100R
Thick Film Resistor, 102Ω, 0.063W, 1%	MC0063W06031102R
Thick Film Resistor, 105Ω, 0.063W, 1%	MC0063W06031105R
Thick Film Resistor, 107Ω, 0.063W, 1%	MC0063W06031107R
Thick Film Resistor, 110Ω, 0.063W, 1%	MC0063W06031110R
Thick Film Resistor, 113Ω, 0.063W, 1%	MC0063W06031113R
Thick Film Resistor, 115Ω, 0.063W, 1%	MC0063W06031115R
Thick Film Resistor, 118Ω, 0.063W, 1%	MC0063W06031118R
Thick Film Resistor, 120Ω, 0.063W, 5%	MC0063W06035120R
Thick Film Resistor, 120Ω, 0.063W, 1%	MC0063W06031120R
Thick Film Resistor, 121Ω, 0.063W, 1%	MC0063W06031121R
Thick Film Resistor, 124Ω, 0.063W, 1%	MC0063W06031124R
Thick Film Resistor, 127Ω, 0.063W, 1%	MC0063W06031127R
Thick Film Resistor, 130Ω, 0.063W, 1%	MC0063W06031130R
Thick Film Resistor, 133Ω, 0.063W, 1%	MC0063W06031133R
Thick Film Resistor, 137Ω, 0.063W, 1%	MC0063W06031137R
Thick Film Resistor, 140Ω, 0.063W, 1%	MC0063W06031140R
Thick Film Resistor, 143Ω, 0.063W, 1%	MC0063W06031143R

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Thick Film Chip Resistor 0603

multicomp PRO

Description	Part Number
Thick Film Resistor, 147Ω, 0.063W, 1%	MC0063W06031147R
Thick Film Resistor, 150Ω, 0.063W, 5%	MC0063W06035150R
Thick Film Resistor, 150Ω, 0.063W, 1%	MC0063W06031150R
Thick Film Resistor, 154Ω, 0.063W, 1%	MC0063W06031154R
Thick Film Resistor, 158Ω, 0.063W, 1%	MC0063W06031158R
Thick Film Resistor, 160Ω, 0.063W, 1%	MC0063W06031160R
Thick Film Resistor, 162Ω, 0.063W, 1%	MC0063W06031162R
Thick Film Resistor, 165Ω, 0.063W, 1%	MC0063W06031165R
Thick Film Resistor, 169Ω, 0.063W, 1%	MC0063W06031169R
Thick Film Resistor, 174Ω, 0.063W, 1%	MC0063W06031174R
Thick Film Resistor, 178Ω, 0.063W, 1%	MC0063W06031178R
Thick Film Resistor, 180Ω, 0.063W, 5%	MC0063W06035180R
Thick Film Resistor, 180Ω, 0.063W, 1%	MC0063W06031180R
Thick Film Resistor, 182Ω, 0.063W, 1%	MC0063W06031182R
Thick Film Resistor, 187Ω, 0.063W, 1%	MC0063W06031187R
Thick Film Resistor, 191Ω, 0.063W, 1%	MC0063W06031191R
Thick Film Resistor, 196Ω, 0.063W, 1%	MC0063W06031196R
Thick Film Resistor, 200Ω, 0.063W, 1%	MC0063W06031200R
Thick Film Resistor, 205Ω, 0.063W, 1%	MC0063W06031205R
Thick Film Resistor, 210Ω, 0.063W, 1%	MC0063W06031210R
Thick Film Resistor, 215Ω, 0.063W, 1%	MC0063W06031215R
Thick Film Resistor, 220Ω, 0.063W, 5%	MC0063W06035220R
Thick Film Resistor, 220Ω, 0.063W, 1%	MC0063W06031220R
Thick Film Resistor, 221Ω, 0.063W, 1%	MC0063W06031221R
Thick Film Resistor, 226Ω, 0.063W, 1%	MC0063W06031226R
Thick Film Resistor, 232Ω, 0.063W, 1%	MC0063W06031232R
Thick Film Resistor, 237Ω, 0.063W, 1%	MC0063W06031237R
Thick Film Resistor, 240Ω, 0.063W, 1%	MC0063W06031240R
Thick Film Resistor, 243Ω, 0.063W, 1%	MC0063W06031243R
Thick Film Resistor, 249Ω, 0.063W, 1%	MC0063W06031249R
Thick Film Resistor, 255Ω, 0.063W, 1%	MC0063W06031255R
Thick Film Resistor, 261Ω, 0.063W, 1%	MC0063W06031261R
Thick Film Resistor, 267Ω, 0.063W, 1%	MC0063W06031267R
Thick Film Resistor, 270Ω, 0.063W, 5%	MC0063W06035270R
Thick Film Resistor, 270Ω, 0.063W, 1%	MC0063W06031270R
Thick Film Resistor, 274Ω, 0.063W, 1%	MC0063W06031274R
Thick Film Resistor, 280Ω, 0.063W, 1%	MC0063W06031280R
Thick Film Resistor, 287Ω, 0.063W, 1%	MC0063W06031287R
Thick Film Resistor, 294Ω, 0.063W, 1%	MC0063W06031294R
Thick Film Resistor, 300Ω, 0.063W, 1%	MC0063W06031300R
Thick Film Resistor, 301Ω, 0.063W, 1%	MC0063W06031301R

Description	Part Number
Thick Film Resistor, 309Ω, 0.063W, 1%	MC0063W06031309R
Thick Film Resistor, 316Ω, 0.063W, 1%	MC0063W06031316R
Thick Film Resistor, 324Ω, 0.063W, 1%	MC0063W06031324R
Thick Film Resistor, 330Ω, 0.063W, 5%	MC0063W06035330R
Thick Film Resistor, 330Ω, 0.063W, 1%	MC0063W06031330R
Thick Film Resistor, 332Ω, 0.063W, 1%	MC0063W06031332R
Thick Film Resistor, 340Ω, 0.063W, 1%	MC0063W06031340R
Thick Film Resistor, 348Ω, 0.063W, 1%	MC0063W06031348R
Thick Film Resistor, 357Ω, 0.063W, 1%	MC0063W06031357R
Thick Film Resistor, 360Ω, 0.063W, 1%	MC0063W06031360R
Thick Film Resistor, 365Ω, 0.063W, 1%	MC0063W06031365R
Thick Film Resistor, 374Ω, 0.063W, 1%	MC0063W06031374R
Thick Film Resistor, 383Ω, 0.063W, 1%	MC0063W06031383R
Thick Film Resistor, 390Ω, 0.063W, 5%	MC0063W06035390R
Thick Film Resistor, 390Ω, 0.063W, 1%	MC0063W06031390R
Thick Film Resistor, 392Ω, 0.063W, 1%	MC0063W06031392R
Thick Film Resistor, 402Ω, 0.063W, 1%	MC0063W06031402R
Thick Film Resistor, 412Ω, 0.063W, 1%	MC0063W06031412R
Thick Film Resistor, 422Ω, 0.063W, 1%	MC0063W06031422R
Thick Film Resistor, 430Ω, 0.063W, 1%	MC0063W06031430R
Thick Film Resistor, 432Ω, 0.063W, 1%	MC0063W06031432R
Thick Film Resistor, 442Ω, 0.063W, 1%	MC0063W06031442R
Thick Film Resistor, 453Ω, 0.063W, 1%	MC0063W06031453R
Thick Film Resistor, 464Ω, 0.063W, 1%	MC0063W06031464R
Thick Film Resistor, 470Ω, 0.063W, 5%	MC0063W06035470R
Thick Film Resistor, 470Ω, 0.063W, 1%	MC0063W06031470R
Thick Film Resistor, 475Ω, 0.063W, 1%	MC0063W06031475R
Thick Film Resistor, 487Ω, 0.063W, 1%	MC0063W06031487R
Thick Film Resistor, 499Ω, 0.063W, 1%	MC0063W06031499R
Thick Film Resistor, 510Ω, 0.063W, 1%	MC0063W06031510R
Thick Film Resistor, 511Ω, 0.063W, 1%	MC0063W06031511R
Thick Film Resistor, 523Ω, 0.063W, 1%	MC0063W06031523R
Thick Film Resistor, 536Ω, 0.063W, 1%	MC0063W06031536R
Thick Film Resistor, 549Ω, 0.063W, 1%	MC0063W06031549R
Thick Film Resistor, 560Ω, 0.063W, 5%	MC0063W06035560R
Thick Film Resistor, 560Ω, 0.063W, 1%	MC0063W06031560R
Thick Film Resistor, 562Ω, 0.063W, 1%	MC0063W06031562R
Thick Film Resistor, 576Ω, 0.063W, 1%	MC0063W06031576R
Thick Film Resistor, 590Ω, 0.063W, 1%	MC0063W06031590R
Thick Film Resistor, 604Ω, 0.063W, 1%	MC0063W06031604R
Thick Film Resistor, 619Ω, 0.063W, 1%	MC0063W06031619R

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Thick Film Chip Resistor 0603

multicomp PRO

Description	Part Number
Thick Film Resistor, 620Ω, 0.063W, 1%	MC0063W06031620R
Thick Film Resistor, 634Ω, 0.063W, 1%	MC0063W06031634R
Thick Film Resistor, 649Ω, 0.063W, 1%	MC0063W06031649R
Thick Film Resistor, 665Ω, 0.063W, 1%	MC0063W06031665R
Thick Film Resistor, 680Ω, 0.063W, 5%	MC0063W06035680R
Thick Film Resistor, 680Ω, 0.063W, 1%	MC0063W06031680R
Thick Film Resistor, 681Ω, 0.063W, 1%	MC0063W06031681R
Thick Film Resistor, 698Ω, 0.063W, 1%	MC0063W06031698R
Thick Film Resistor, 715Ω, 0.063W, 1%	MC0063W06031715R
Thick Film Resistor, 732Ω, 0.063W, 1%	MC0063W06031732R
Thick Film Resistor, 750Ω, 0.063W, 1%	MC0063W06031750R
Thick Film Resistor, 768Ω, 0.063W, 1%	MC0063W06031768R
Thick Film Resistor, 787Ω, 0.063W, 1%	MC0063W06031787R
Thick Film Resistor, 806Ω, 0.063W, 1%	MC0063W06031806R
Thick Film Resistor, 820Ω, 0.063W, 5%	MC0063W06035820R
Thick Film Resistor, 820Ω, 0.063W, 1%	MC0063W06031820R
Thick Film Resistor, 825Ω, 0.063W, 1%	MC0063W06031825R
Thick Film Resistor, 845Ω, 0.063W, 1%	MC0063W06031845R
Thick Film Resistor, 866Ω, 0.063W, 1%	MC0063W06031866R
Thick Film Resistor, 887Ω, 0.063W, 1%	MC0063W06031887R
Thick Film Resistor, 909Ω, 0.063W, 1%	MC0063W06031909R
Thick Film Resistor, 910Ω, 0.063W, 1%	MC0063W06031910R
Thick Film Resistor, 931Ω, 0.063W, 1%	MC0063W06031931R
Thick Film Resistor, 953Ω, 0.063W, 1%	MC0063W06031953R
Thick Film Resistor, 976Ω, 0.063W, 1%	MC0063W06031976R
Thick Film Resistor, 1kΩ, 0.063W, 1%	MC0063W060351K
Thick Film Resistor, 1kΩ, 0.063W, 1%	MC0063W060311K
Thick Film Resistor, 1.02kΩ, 0.063W, 1%	MC0063W060311K02
Thick Film Resistor, 1.05kΩ, 0.063W, 1%	MC0063W060311K05
Thick Film Resistor, 1.07kΩ, 0.063W, 1%	MC0063W060311K07
Thick Film Resistor, 1.1kΩ, 0.063W, 1%	MC0063W060311K1
Thick Film Resistor, 1.13kΩ, 0.063W, 1%	MC0063W060311K13
Thick Film Resistor, 1.15kΩ, 0.063W, 1%	MC0063W060311K15
Thick Film Resistor, 1.18kΩ, 0.063W, 1%	MC0063W060311K18
Thick Film Resistor, 1.2kΩ, 0.063W, 5%	MC0063W060351K2
Thick Film Resistor, 1.2kΩ, 0.063W, 1%	MC0063W060311K2
Thick Film Resistor, 1.21kΩ, 0.063W, 1%	MC0063W060311K21
Thick Film Resistor, 1.24kΩ, 0.063W, 1%	MC0063W060311K24
Thick Film Resistor, 1.27kΩ, 0.063W, 1%	MC0063W060311K27
Thick Film Resistor, 1.3kΩ, 0.063W, 1%	MC0063W060311K3
Thick Film Resistor, 1.33kΩ, 0.063W, 1%	MC0063W060311K33

Description	Part Number
Thick Film Resistor, 1.37kΩ, 0.063W, 1%	MC0063W060311K37
Thick Film Resistor, 1.4kΩ, 0.063W, 1%	MC0063W060311K4
Thick Film Resistor, 1.43kΩ, 0.063W, 1%	MC0063W060311K43
Thick Film Resistor, 1.47kΩ, 0.063W, 1%	MC0063W060311K47
Thick Film Resistor, 1.5kΩ, 0.063W, 5%	MC0063W060351K5
Thick Film Resistor, 1.5kΩ, 0.063W, 1%	MC0063W060311K5
Thick Film Resistor, 1.54kΩ, 0.063W, 1%	MC0063W060311K54
Thick Film Resistor, 1.58kΩ, 0.063W, 1%	MC0063W060311K58
Thick Film Resistor, 1.6kΩ, 0.063W, 1%	MC0063W060311K6
Thick Film Resistor, 1.62kΩ, 0.063W, 1%	MC0063W060311K62
Thick Film Resistor, 1.65kΩ, 0.063W, 1%	MC0063W060311K65
Thick Film Resistor, 1.69kΩ, 0.063W, 1%	MC0063W060311K69
Thick Film Resistor, 1.74kΩ, 0.063W, 1%	MC0063W060311K74
Thick Film Resistor, 1.78kΩ, 0.063W, 1%	MC0063W060311K78
Thick Film Resistor, 1.8kΩ, 0.063W, 5%	MC0063W060351K8
Thick Film Resistor, 1.8kΩ, 0.063W, 1%	MC0063W060311K8
Thick Film Resistor, 1.82kΩ, 0.063W, 1%	MC0063W060311K82
Thick Film Resistor, 1.87kΩ, 0.063W, 1%	MC0063W060311K87
Thick Film Resistor, 1.91kΩ, 0.063W, 1%	MC0063W060311K91
Thick Film Resistor, 1.96kΩ, 0.063W, 1%	MC0063W060311K96
Thick Film Resistor, 2kΩ, 0.063W, 1%	MC0063W060312K
Thick Film Resistor, 2.05kΩ, 0.063W, 1%	MC0063W060312K05
Thick Film Resistor, 2.1kΩ, 0.063W, 1%	MC0063W060312K1
Thick Film Resistor, 2.15kΩ, 0.063W, 1%	MC0063W060312K15
Thick Film Resistor, 2.2kΩ, 0.063W, 1%	MC0063W060352K2
Thick Film Resistor, 2.2kΩ, 0.063W, 1%	MC0063W060312K2
Thick Film Resistor, 2.21kΩ, 0.063W, 1%	MC0063W060312K21
Thick Film Resistor, 2.26kΩ, 0.063W, 1%	MC0063W060312K26
Thick Film Resistor, 2.32kΩ, 0.063W, 1%	MC0063W060312K32
Thick Film Resistor, 2.37kΩ, 0.063W, 1%	MC0063W060312K37
Thick Film Resistor, 2.4kΩ, 0.063W, 1%	MC0063W060312K4
Thick Film Resistor, 2.43kΩ, 0.063W, 1%	MC0063W060312K43
Thick Film Resistor, 2.49kΩ, 0.063W, 1%	MC0063W060312K49
Thick Film Resistor, 2.55kΩ, 0.063W, 1%	MC0063W060312K55
Thick Film Resistor, 2.61kΩ, 0.063W, 1%	MC0063W060312K61
Thick Film Resistor, 2.67kΩ, 0.063W, 1%	MC0063W060312K67
Thick Film Resistor, 2.7kΩ, 0.063W, 5%	MC0063W060352K7
Thick Film Resistor, 2.7kΩ, 0.063W, 1%	MC0063W060312K7
Thick Film Resistor, 2.74kΩ, 0.063W, 1%	MC0063W060312K74
Thick Film Resistor, 2.8kΩ, 0.063W, 1%	MC0063W060312K8
Thick Film Resistor, 2.87kΩ, 0.063W, 1%	MC0063W060312K87

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Thick Film Chip Resistor 0603

multicomp PRO

Description	Part Number
Thick Film Resistor, 2.94kΩ, 0.063W, 1%	MC0063W060312K94
Thick Film Resistor, 3kΩ, 0.063W, 1%	MC0063W060313K
Thick Film Resistor, 3.01kΩ, 0.063W, 1%	MC0063W060313K01
Thick Film Resistor, 3.09kΩ, 0.063W, 1%	MC0063W060313K09
Thick Film Resistor, 3.16kΩ, 0.063W, 1%	MC0063W060313K16
Thick Film Resistor, 3.24kΩ, 0.063W, 1%	MC0063W060313K24
Thick Film Resistor, 3.3kΩ, 0.063W, 5%	MC0063W060353K3
Thick Film Resistor, 3.3kΩ, 0.063W, 1%	MC0063W060313K3
Thick Film Resistor, 3.32kΩ, 0.063W, 1%	MC0063W060313K32
Thick Film Resistor, 3.4kΩ, 0.063W, 1%	MC0063W060313K4
Thick Film Resistor, 3.48kΩ, 0.063W, 1%	MC0063W060313K48
Thick Film Resistor, 3.57kΩ, 0.063W, 1%	MC0063W060313K57
Thick Film Resistor, 3.6kΩ, 0.063W, 1%	MC0063W060313K6
Thick Film Resistor, 3.65kΩ, 0.063W, 1%	MC0063W060313K65
Thick Film Resistor, 3.74kΩ, 0.063W, 1%	MC0063W060313K74
Thick Film Resistor, 3.83kΩ, 0.063W, 1%	MC0063W060313K83
Thick Film Resistor, 3.9kΩ, 0.063W, 5%	MC0063W060353K9
Thick Film Resistor, 3.9kΩ, 0.063W, 1%	MC0063W060313K9
Thick Film Resistor, 3.92kΩ, 0.063W, 1%	MC0063W060313K92
Thick Film Resistor, 4.02kΩ, 0.063W, 1%	MC0063W060314K02
Thick Film Resistor, 4.12kΩ, 0.063W, 1%	MC0063W060314K12
Thick Film Resistor, 4.22kΩ, 0.063W, 1%	MC0063W060314K22
Thick Film Resistor, 4.3kΩ, 0.063W, 1%	MC0063W060314K3
Thick Film Resistor, 4.32kΩ, 0.063W, 1%	MC0063W060314K32
Thick Film Resistor, 4.42kΩ, 0.063W, 1%	MC0063W060314K42
Thick Film Resistor, 4.53kΩ, 0.063W, 1%	MC0063W060314K53
Thick Film Resistor, 4.64kΩ, 0.063W, 1%	MC0063W060314K64
Thick Film Resistor, 4.7kΩ, 0.063W, 1%	MC0063W060354K7
Thick Film Resistor, 4.7kΩ, 0.063W, 1%	MC0063W060314K7
Thick Film Resistor, 4.7kΩ, 0.063W, 1%	MC0603WGF4701T5E-TC
Thick Film Resistor, 4.75kΩ, 0.063W, 1%	MC0063W060314K75
Thick Film Resistor, 4.87kΩ, 0.063W, 1%	MC0063W060314K87
Thick Film Resistor, 4.99kΩ, 0.063W, 1%	MC0063W060314K99
Thick Film Resistor, 5.1kΩ, 0.063W, 1%	MC0063W060315K1
Thick Film Resistor, 5.11kΩ, 0.063W, 1%	MC0063W060315K11
Thick Film Resistor, 5.23kΩ, 0.063W, 1%	MC0063W060315K23
Thick Film Resistor, 5.36kΩ, 0.063W, 1%	MC0063W060315K36
Thick Film Resistor, 5.49kΩ, 0.063W, 1%	MC0063W060315K49
Thick Film Resistor, 5.6kΩ, 0.063W, 5%	MC0063W060355K6
Thick Film Resistor, 5.6kΩ, 0.063W, 1%	MC0063W060315K6
Thick Film Resistor, 5.62kΩ, 0.063W, 1%	MC0063W060315K62

Description	Part Number
Thick Film Resistor, 5.76kΩ, 0.063W, 1%	MC0063W060315K76
Thick Film Resistor, 5.9kΩ, 0.063W, 1%	MC0063W060315K9
Thick Film Resistor, 6.04kΩ, 0.063W, 1%	MC0063W060316K04
Thick Film Resistor, 6.19kΩ, 0.063W, 1%	MC0063W060316K19
Thick Film Resistor, 6.2kΩ, 0.063W, 1%	MC0063W060316K2
Thick Film Resistor, 6.34kΩ, 0.063W, 1%	MC0063W060316K34
Thick Film Resistor, 6.49kΩ, 0.063W, 1%	MC0063W060316K49
Thick Film Resistor, 6.65kΩ, 0.063W, 1%	MC0063W060316K65
Thick Film Resistor, 6.8kΩ, 0.063W, 5%	MC0063W060356K8
Thick Film Resistor, 6.8kΩ, 0.063W, 1%	MC0063W060316K8
Thick Film Resistor, 6.81kΩ, 0.063W, 1%	MC0063W060316K81
Thick Film Resistor, 6.98kΩ, 0.063W, 1%	MC0063W060316K98
Thick Film Resistor, 7.15kΩ, 0.063W, 1%	MC0063W060317K15
Thick Film Resistor, 7.32kΩ, 0.063W, 1%	MC0063W060317K32
Thick Film Resistor, 7.5kΩ, 0.063W, 1%	MC0063W060317K5
Thick Film Resistor, 7.68kΩ, 0.063W, 1%	MC0063W060317K68
Thick Film Resistor, 7.87kΩ, 0.063W, 1%	MC0063W060317K87
Thick Film Resistor, 8.06kΩ, 0.063W, 1%	MC0063W060318K06
Thick Film Resistor, 8.2kΩ, 0.063W, 5%	MC0063W060358K2
Thick Film Resistor, 8.2kΩ, 0.063W, 1%	MC0063W060318K2
Thick Film Resistor, 8.25kΩ, 0.063W, 1%	MC0063W060318K25
Thick Film Resistor, 8.45kΩ, 0.063W, 1%	MC0063W060318K45
Thick Film Resistor, 8.66kΩ, 0.063W, 1%	MC0063W060318K66
Thick Film Resistor, 8.87kΩ, 0.063W, 1%	MC0063W060318K87
Thick Film Resistor, 9.09kΩ, 0.063W, 1%	MC0063W060319K09
Thick Film Resistor, 9.1kΩ, 0.063W, 1%	MC0063W060319K1
Thick Film Resistor, 9.53kΩ, 0.063W, 1%	MC0063W060319K53
Thick Film Resistor, 9.76kΩ, 0.063W, 1%	MC0063W060319K76
Thick Film Resistor, 10kΩ, 0.063W, 1%	MC0063W0603510K
Thick Film Resistor, 10kΩ, 0.063W, 1%	MC0063W0603110K
Thick Film Resistor, 10.2kΩ, 0.063W, 1%	MC0063W0603110K2
Thick Film Resistor, 10.5kΩ, 0.063W, 1%	MC0063W0603110K5
Thick Film Resistor, 10.7kΩ, 0.063W, 1%	MC0063W0603110K7
Thick Film Resistor, 11kΩ, 0.063W, 1%	MC0063W0603111K
Thick Film Resistor, 11.3kΩ, 0.063W, 1%	MC0063W0603111K3
Thick Film Resistor, 11.5kΩ, 0.063W, 1%	MC0063W0603111K5
Thick Film Resistor, 11.8kΩ, 0.063W, 1%	MC0063W0603111K8
Thick Film Resistor, 12kΩ, 0.063W, 5%	MC0063W0603512K
Thick Film Resistor, 12kΩ, 0.063W, 1%	MC0063W0603112K
Thick Film Resistor, 12.1kΩ, 0.063W, 1%	MC0063W0603112K1
Thick Film Resistor, 12.4kΩ, 0.063W, 1%	MC0063W0603112K4

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Thick Film Chip Resistor 0603

multicomp PRO

Description	Part Number
Thick Film Resistor, 12.7kΩ, 0.063W, 1%	MC0063W0603112K7
Thick Film Resistor, 13kΩ, 0.063W, 1%	MC0063W0603113K
Thick Film Resistor, 13.3kΩ, 0.063W, 1%	MC0063W0603113K3
Thick Film Resistor, 13.7kΩ, 0.063W, 1%	MC0063W0603113K7
Thick Film Resistor, 14kΩ, 0.063W, 1%	MC0063W0603114K
Thick Film Resistor, 14.3kΩ, 0.063W, 1%	MC0063W0603114K3
Thick Film Resistor, 14.7kΩ, 0.063W, 1%	MC0063W0603114K7
Thick Film Resistor, 15kΩ, 0.063W, 5%	MC0063W0603515K
Thick Film Resistor, 15kΩ, 0.063W, 1%	MC0063W0603115K
Thick Film Resistor, 15.4kΩ, 0.063W, 1%	MC0063W0603115K4
Thick Film Resistor, 15.8kΩ, 0.063W, 1%	MC0063W0603115K8
Thick Film Resistor, 16kΩ, 0.063W, 1%	MC0063W0603116K
Thick Film Resistor, 16.2kΩ, 0.063W, 1%	MC0063W0603116K2
Thick Film Resistor, 16.5kΩ, 0.063W, 1%	MC0063W0603116K5
Thick Film Resistor, 16.9kΩ, 0.063W, 1%	MC0063W0603116K9
Thick Film Resistor, 17.4kΩ, 0.063W, 1%	MC0063W0603117K4
Thick Film Resistor, 17.8kΩ, 0.063W, 1%	MC0063W0603117K8
Thick Film Resistor, 18kΩ, 0.063W, 5%	MC0063W0603518K
Thick Film Resistor, 18kΩ, 0.063W, 1%	MC0063W0603118K
Thick Film Resistor, 18.2kΩ, 0.063W, 1%	MC0063W0603118K2
Thick Film Resistor, 18.7kΩ, 0.063W, 1%	MC0063W0603118K7
Thick Film Resistor, 19.1kΩ, 0.063W, 1%	MC0063W0603119K1
Thick Film Resistor, 19.6kΩ, 0.063W, 1%	MC0063W0603119K6
Thick Film Resistor, 20kΩ, 0.063W, 1%	MC0063W0603120K
Thick Film Resistor, 20kΩ, 0.063W, 1%	MC0603WGF2002T5E-TC
Thick Film Resistor, 20.5kΩ, 0.063W, 1%	MC0063W0603120K5
Thick Film Resistor, 21kΩ, 0.063W, 1%	MC0063W0603121K
Thick Film Resistor, 21.5kΩ, 0.063W, 1%	MC0063W0603121K5
Thick Film Resistor, 22kΩ, 0.063W, 5%	MC0063W0603522K
Thick Film Resistor, 22kΩ, 0.063W, 1%	MC0063W0603122K
Thick Film Resistor, 22.1kΩ, 0.063W, 1%	MC0063W0603122K1
Thick Film Resistor, 22.6kΩ, 0.063W, 1%	MC0063W0603122K6
Thick Film Resistor, 23.2kΩ, 0.063W, 1%	MC0063W0603123K2
Thick Film Resistor, 23.7kΩ, 0.063W, 1%	MC0063W0603123K7
Thick Film Resistor, 24kΩ, 0.063W, 1%	MC0063W0603124K
Thick Film Resistor, 24.3kΩ, 0.063W, 1%	MC0063W0603124K3
Thick Film Resistor, 24.9kΩ, 0.063W, 1%	MC0063W0603124K9
Thick Film Resistor, 25.5kΩ, 0.063W, 1%	MC0063W0603125K5
Thick Film Resistor, 26.1kΩ, 0.063W, 1%	MC0063W0603126K1
Thick Film Resistor, 26.7kΩ, 0.063W, 1%	MC0063W0603126K7
Thick Film Resistor, 27kΩ, 0.063W, 5%	MC0063W0603527K

Description	Part Number
Thick Film Resistor, 27kΩ, 0.063W, 1%	MC0063W0603127K
Thick Film Resistor, 27.4kΩ, 0.063W, 1%	MC0063W0603127K4
Thick Film Resistor, 28kΩ, 0.063W, 1%	MC0063W0603128K
Thick Film Resistor, 28.7kΩ, 0.063W, 1%	MC0063W0603128K7
Thick Film Resistor, 29.4kΩ, 0.063W, 1%	MC0063W0603129K4
Thick Film Resistor, 30kΩ, 0.063W, 1%	MC0063W0603130K
Thick Film Resistor, 30.1kΩ, 0.063W, 1%	MC0063W0603130K1
Thick Film Resistor, 30.9kΩ, 0.063W, 1%	MC0063W0603130K9
Thick Film Resistor, 31.6kΩ, 0.063W, 1%	MC0063W0603131K6
Thick Film Resistor, 32.4kΩ, 0.063W, 1%	MC0063W0603132K4
Thick Film Resistor, 33kΩ, 0.063W, 5%	MC0063W0603533K
Thick Film Resistor, 33kΩ, 0.063W, 1%	MC0063W0603133K
Thick Film Resistor, 33.2kΩ, 0.063W, 1%	MC0063W0603133K2
Thick Film Resistor, 34kΩ, 0.063W, 1%	MC0063W0603134K
Thick Film Resistor, 34.8kΩ, 0.063W, 1%	MC0063W0603134K8
Thick Film Resistor, 35.7kΩ, 0.063W, 1%	MC0063W0603135K7
Thick Film Resistor, 36kΩ, 0.063W, 1%	MC0063W0603136K
Thick Film Resistor, 36.5kΩ, 0.063W, 1%	MC0063W0603136K5
Thick Film Resistor, 37.4kΩ, 0.063W, 1%	MC0063W0603137K4
Thick Film Resistor, 38.3kΩ, 0.063W, 1%	MC0063W0603138K3
Thick Film Resistor, 39kΩ, 0.063W, 5%	MC0063W0603539K
Thick Film Resistor, 39kΩ, 0.063W, 1%	MC0063W0603139K
Thick Film Resistor, 39.2kΩ, 0.063W, 1%	MC0063W0603139K2
Thick Film Resistor, 40.2kΩ, 0.063W, 1%	MC0063W0603140K2
Thick Film Resistor, 41.2kΩ, 0.063W, 1%	MC0063W0603141K2
Thick Film Resistor, 42.2kΩ, 0.063W, 1%	MC0063W0603142K2
Thick Film Resistor, 43kΩ, 0.063W, 1%	MC0063W0603143K
Thick Film Resistor, 43.2kΩ, 0.063W, 1%	MC0063W0603143K2
Thick Film Resistor, 44.2kΩ, 0.063W, 1%	MC0063W0603144K2
Thick Film Resistor, 45.3kΩ, 0.063W, 1%	MC0063W0603145K3
Thick Film Resistor, 46.4kΩ, 0.063W, 1%	MC0063W0603146K4
Thick Film Resistor, 47kΩ, 0.063W, 5%	MC0063W0603547K
Thick Film Resistor, 47kΩ, 0.063W, 1%	MC0063W0603147K
Thick Film Resistor, 47kΩ, 0.063W, 1%	MC0603WGF4702T5E-TC
Thick Film Resistor, 47.5kΩ, 0.063W, 1%	MC0063W0603147K5
Thick Film Resistor, 48.7kΩ, 0.063W, 1%	MC0063W0603148K7
Thick Film Resistor, 49.9kΩ, 0.063W, 1%	MC0063W0603149K9
Thick Film Resistor, 51kΩ, 0.063W, 1%	MC0063W0603151K
Thick Film Resistor, 51.1kΩ, 0.063W, 1%	MC0063W0603151K1
Thick Film Resistor, 52.3kΩ, 0.063W, 1%	MC0063W0603152K3
Thick Film Resistor, 53.6kΩ, 0.063W, 1%	MC0063W0603153K6

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Thick Film Chip Resistor 0603

multicomp PRO

Description	Part Number
Thick Film Resistor, 54.9kΩ, 0.063W, 1%	MC0063W0603154K9
Thick Film Resistor, 56kΩ, 0.063W, 5%	MC0063W0603556K
Thick Film Resistor, 56kΩ, 0.063W, 1%	MC0063W0603156K
Thick Film Resistor, 56.2kΩ, 0.063W, 1%	MC0063W0603156K2
Thick Film Resistor, 57.6kΩ, 0.063W, 1%	MC0063W0603157K6
Thick Film Resistor, 59kΩ, 0.063W, 1%	MC0063W0603159K
Thick Film Resistor, 60.4kΩ, 0.063W, 1%	MC0063W0603160K4
Thick Film Resistor, 61.9kΩ, 0.063W, 1%	MC0063W0603161K9
Thick Film Resistor, 62kΩ, 0.063W, 1%	MC0063W0603162K
Thick Film Resistor, 63.4kΩ, 0.063W, 1%	MC0063W0603163K4
Thick Film Resistor, 64.9kΩ, 0.063W, 1%	MC0063W0603164K9
Thick Film Resistor, 66.5kΩ, 0.063W, 1%	MC0063W0603166K5
Thick Film Resistor, 68kΩ, 0.063W, 5%	MC0063W0603568K
Thick Film Resistor, 68kΩ, 0.063W, 1%	MC0063W0603168K
Thick Film Resistor, 68.1kΩ, 0.063W, 1%	MC0063W0603168K1
Thick Film Resistor, 69.8kΩ, 0.063W, 1%	MC0063W0603169K8
Thick Film Resistor, 71.5kΩ, 0.063W, 1%	MC0063W0603171K5
Thick Film Resistor, 73.2kΩ, 0.063W, 1%	MC0063W0603173K2
Thick Film Resistor, 75kΩ, 0.063W, 1%	MC0063W0603175K
Thick Film Resistor, 76.8kΩ, 0.063W, 1%	MC0063W0603176K8
Thick Film Resistor, 78.7kΩ, 0.063W, 1%	MC0063W0603178K7
Thick Film Resistor, 80.6kΩ, 0.063W, 1%	MC0063W0603180K6
Thick Film Resistor, 82kΩ, 0.063W, 5%	MC0063W0603582K
Thick Film Resistor, 82kΩ, 0.063W, 1%	MC0063W0603182K
Thick Film Resistor, 82.5kΩ, 0.063W, 1%	MC0063W0603182K5
Thick Film Resistor, 84.5kΩ, 0.063W, 1%	MC0063W0603184K5
Thick Film Resistor, 86.6kΩ, 0.063W, 1%	MC0063W0603186K6
Thick Film Resistor, 88.7kΩ, 0.063W, 1%	MC0063W0603188K7
Thick Film Resistor, 90.9kΩ, 0.063W, 1%	MC0063W0603190K9
Thick Film Resistor, 91kΩ, 0.063W, 1%	MC0063W0603191K
Thick Film Resistor, 93.1kΩ, 0.063W, 1%	MC0063W0603193K1
Thick Film Resistor, 95.3kΩ, 0.063W, 1%	MC0063W0603195K3
Thick Film Resistor, 97.6kΩ, 0.063W, 1%	MC0063W0603197K6
Thick Film Resistor, 100kΩ, 0.063W, 1%	MC0063W06035100K
Thick Film Resistor, 100kΩ, 0.063W, 1%	MC0063W06031100K
Thick Film Resistor, 100kΩ, 0.063W, 1%	MC0603WGF1003T5E-TR
Thick Film Resistor, 102kΩ, 0.063W, 1%	MC0063W06031102K
Thick Film Resistor, 105kΩ, 0.063W, 1%	MC0063W06031105K
Thick Film Resistor, 107kΩ, 0.063W, 1%	MC0063W06031107K
Thick Film Resistor, 110kΩ, 0.063W, 1%	MC0063W06031110K
Thick Film Resistor, 113kΩ, 0.063W, 1%	MC0063W06031113K

Description	Part Number
Thick Film Resistor, 115kΩ, 0.063W, 1%	MC0063W06031115K
Thick Film Resistor, 118kΩ, 0.063W, 1%	MC0063W06031118K
Thick Film Resistor, 120kΩ, 0.063W, 5%	MC0063W06035120K
Thick Film Resistor, 120kΩ, 0.063W, 1%	MC0063W06031120K
Thick Film Resistor, 121kΩ, 0.063W, 1%	MC0063W06031121K
Thick Film Resistor, 124kΩ, 0.063W, 1%	MC0063W06031124K
Thick Film Resistor, 127kΩ, 0.063W, 1%	MC0063W06031127K
Thick Film Resistor, 130kΩ, 0.063W, 1%	MC0063W06031130K
Thick Film Resistor, 133kΩ, 0.063W, 1%	MC0063W06031133K
Thick Film Resistor, 137kΩ, 0.063W, 1%	MC0063W06031137K
Thick Film Resistor, 140kΩ, 0.063W, 1%	MC0063W06031140K
Thick Film Resistor, 143kΩ, 0.063W, 1%	MC0063W06031143K
Thick Film Resistor, 147kΩ, 0.063W, 1%	MC0063W06031147K
Thick Film Resistor, 150kΩ, 0.063W, 5%	MC0063W06035150K
Thick Film Resistor, 150kΩ, 0.063W, 1%	MC0063W06031150K
Thick Film Resistor, 154kΩ, 0.063W, 1%	MC0063W06031154K
Thick Film Resistor, 158kΩ, 0.063W, 1%	MC0063W06031158K
Thick Film Resistor, 160kΩ, 0.063W, 1%	MC0063W06031160K
Thick Film Resistor, 162kΩ, 0.063W, 1%	MC0063W06031162K
Thick Film Resistor, 165kΩ, 0.063W, 1%	MC0063W06031165K
Thick Film Resistor, 169kΩ, 0.063W, 1%	MC0063W06031169K
Thick Film Resistor, 174kΩ, 0.063W, 1%	MC0063W06031174K
Thick Film Resistor, 178kΩ, 0.063W, 1%	MC0063W06031178K
Thick Film Resistor, 180kΩ, 0.063W, 5%	MC0063W06035180K
Thick Film Resistor, 180kΩ, 0.063W, 1%	MC0063W06031180K
Thick Film Resistor, 182kΩ, 0.063W, 1%	MC0063W06031182K
Thick Film Resistor, 187kΩ, 0.063W, 1%	MC0063W06031187K
Thick Film Resistor, 191kΩ, 0.063W, 1%	MC0063W06031191K
Thick Film Resistor, 196kΩ, 0.063W, 1%	MC0063W06031196K
Thick Film Resistor, 200kΩ, 0.063W, 1%	MC0063W06031200K
Thick Film Resistor, 205kΩ, 0.063W, 1%	MC0063W06031205K
Thick Film Resistor, 210kΩ, 0.063W, 1%	MC0063W06031210K
Thick Film Resistor, 215kΩ, 0.063W, 1%	MC0063W06031215K
Thick Film Resistor, 220kΩ, 0.063W, 5%	MC0063W06035220K
Thick Film Resistor, 220kΩ, 0.063W, 1%	MC0063W06031220K
Thick Film Resistor, 221kΩ, 0.063W, 1%	MC0063W06031221K
Thick Film Resistor, 226kΩ, 0.063W, 1%	MC0063W06031226K
Thick Film Resistor, 232kΩ, 0.063W, 1%	MC0063W06031232K
Thick Film Resistor, 237kΩ, 0.063W, 1%	MC0063W06031237K
Thick Film Resistor, 240kΩ, 0.063W, 1%	MC0063W06031240K
Thick Film Resistor, 243kΩ, 0.063W, 1%	MC0063W06031243K

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Thick Film Chip Resistor 0603

multicomp PRO

Description	Part Number
Thick Film Resistor, 249kΩ, 0.063W, 1%	MC0063W06031249K
Thick Film Resistor, 255kΩ, 0.063W, 1%	MC0063W06031255K
Thick Film Resistor, 261kΩ, 0.063W, 1%	MC0063W06031261K
Thick Film Resistor, 267kΩ, 0.063W, 1%	MC0063W06031267K
Thick Film Resistor, 270kΩ, 0.063W, 5%	MC0063W06035270K
Thick Film Resistor, 270kΩ, 0.063W, 1%	MC0063W06031270K
Thick Film Resistor, 274kΩ, 0.063W, 1%	MC0063W06031274K
Thick Film Resistor, 287kΩ, 0.063W, 1%	MC0063W06031287K
Thick Film Resistor, 294kΩ, 0.063W, 1%	MC0063W06031294K
Thick Film Resistor, 300kΩ, 0.063W, 1%	MC0063W06031300K
Thick Film Resistor, 301kΩ, 0.063W, 1%	MC0063W06031301K
Thick Film Resistor, 309kΩ, 0.063W, 1%	MC0063W06031309K
Thick Film Resistor, 316kΩ, 0.063W, 1%	MC0063W06031316K
Thick Film Resistor, 324kΩ, 0.063W, 1%	MC0063W06031324K
Thick Film Resistor, 330kΩ, 0.063W, 5%	MC0063W06035330K
Thick Film Resistor, 330kΩ, 0.063W, 1%	MC0063W06031330K
Thick Film Resistor, 332kΩ, 0.063W, 1%	MC0063W06031332K
Thick Film Resistor, 340kΩ, 0.063W, 1%	MC0063W06031340K
Thick Film Resistor, 348kΩ, 0.063W, 1%	MC0063W06031348K
Thick Film Resistor, 357kΩ, 0.063W, 1%	MC0063W06031357K
Thick Film Resistor, 360kΩ, 0.063W, 1%	MC0063W06031360K
Thick Film Resistor, 365kΩ, 0.063W, 1%	MC0063W06031365K
Thick Film Resistor, 374kΩ, 0.063W, 1%	MC0063W06031374K
Thick Film Resistor, 383kΩ, 0.063W, 1%	MC0063W06031383K
Thick Film Resistor, 390kΩ, 0.063W, 5%	MC0063W06035390K
Thick Film Resistor, 390kΩ, 0.063W, 1%	MC0063W06031390K
Thick Film Resistor, 392kΩ, 0.063W, 1%	MC0063W06031392K
Thick Film Resistor, 402kΩ, 0.063W, 1%	MC0063W06031402K
Thick Film Resistor, 412kΩ, 0.063W, 1%	MC0063W06031412K
Thick Film Resistor, 422kΩ, 0.063W, 1%	MC0063W06031422K
Thick Film Resistor, 430kΩ, 0.063W, 1%	MC0063W06031430K
Thick Film Resistor, 432kΩ, 0.063W, 1%	MC0063W06031432K
Thick Film Resistor, 442kΩ, 0.063W, 1%	MC0063W06031442K
Thick Film Resistor, 453kΩ, 0.063W, 1%	MC0063W06031453K
Thick Film Resistor, 464kΩ, 0.063W, 1%	MC0063W06031464K
Thick Film Resistor, 470kΩ, 0.063W, 5%	MC0063W06035470K
Thick Film Resistor, 470kΩ, 0.063W, 1%	MC0063W06031470K
Thick Film Resistor, 475kΩ, 0.063W, 1%	MC0063W06031475K
Thick Film Resistor, 487kΩ, 0.063W, 1%	MC0063W06031487K
Thick Film Resistor, 499kΩ, 0.063W, 1%	MC0063W06031499K
Thick Film Resistor, 510kΩ, 0.063W, 1%	MC0063W06031510K

Description	Part Number
Thick Film Resistor, 511kΩ, 0.063W, 1%	MC0063W06031511K
Thick Film Resistor, 523kΩ, 0.063W, 1%	MC0063W06031523K
Thick Film Resistor, 536kΩ, 0.063W, 1%	MC0063W06031536K
Thick Film Resistor, 549kΩ, 0.063W, 1%	MC0063W06031549K
Thick Film Resistor, 560kΩ, 0.063W, 5%	MC0063W06035560K
Thick Film Resistor, 560kΩ, 0.063W, 1%	MC0063W06031560K
Thick Film Resistor, 562kΩ, 0.063W, 1%	MC0063W06031562K
Thick Film Resistor, 576kΩ, 0.063W, 1%	MC0063W06031576K
Thick Film Resistor, 590kΩ, 0.063W, 1%	MC0063W06031590K
Thick Film Resistor, 604kΩ, 0.063W, 1%	MC0063W06031604K
Thick Film Resistor, 619kΩ, 0.063W, 1%	MC0063W06031619K
Thick Film Resistor, 620kΩ, 0.063W, 1%	MC0063W06031620K
Thick Film Resistor, 634kΩ, 0.063W, 1%	MC0063W06031634K
Thick Film Resistor, 649kΩ, 0.063W, 1%	MC0063W06031649K
Thick Film Resistor, 665kΩ, 0.063W, 1%	MC0063W06031665K
Thick Film Resistor, 680kΩ, 0.063W, 5%	MC0063W06035680K
Thick Film Resistor, 680kΩ, 0.063W, 1%	MC0063W06031680K
Thick Film Resistor, 681kΩ, 0.063W, 1%	MC0063W06031681K
Thick Film Resistor, 698kΩ, 0.063W, 1%	MC0063W06031698K
Thick Film Resistor, 715kΩ, 0.063W, 1%	MC0063W06031715K
Thick Film Resistor, 732kΩ, 0.063W, 1%	MC0063W06031732K
Thick Film Resistor, 750kΩ, 0.063W, 1%	MC0063W06031750K
Thick Film Resistor, 768kΩ, 0.063W, 1%	MC0063W06031768K
Thick Film Resistor, 787kΩ, 0.063W, 1%	MC0063W06031787K
Thick Film Resistor, 806kΩ, 0.063W, 1%	MC0063W06031806K
Thick Film Resistor, 820kΩ, 0.063W, 5%	MC0063W06035820K
Thick Film Resistor, 820kΩ, 0.063W, 1%	MC0063W06031820K
Thick Film Resistor, 825kΩ, 0.063W, 1%	MC0063W06031825K
Thick Film Resistor, 845kΩ, 0.063W, 1%	MC0063W06031845K
Thick Film Resistor, 866kΩ, 0.063W, 1%	MC0063W06031866K
Thick Film Resistor, 887kΩ, 0.063W, 1%	MC0063W06031887K
Thick Film Resistor, 909kΩ, 0.063W, 1%	MC0063W06031909K
Thick Film Resistor, 910kΩ, 0.063W, 1%	MC0063W06031910K
Thick Film Resistor, 931kΩ, 0.063W, 1%	MC0063W06031931K
Thick Film Resistor, 953kΩ, 0.063W, 1%	MC0063W06031953K
Thick Film Resistor, 976kΩ, 0.063W, 1%	MC0063W06031976K
Thick Film Resistor, 1MΩ, 0.063W, 1%	MC0063W060311M
Thick Film Resistor, 1MΩ, 0.063W, 5%	MC0063W060351M
Thick Film Resistor, 1.05MΩ, 0.063W, 1%	MC0063W060311M05
Thick Film Resistor, 1.1MΩ, 0.063W, 1%	MC0063W060311M10
Thick Film Resistor, 1.15MΩ, 0.063W, 1%	MC0063W060311M15

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Thick Film Chip Resistor 0603

multicomp PRO

Description	Part Number
Thick Film Resistor, 1.2MΩ, 0.063W, 1%	MC0063W060311M20
Thick Film Resistor, 1.21MΩ, 0.063W, 1%	MC0063W060311M21
Thick Film Resistor, 1.27MΩ, 0.063W, 1%	MC0063W060311M27
Thick Film Resistor, 1.3MΩ, 0.063W, 1%	MC0063W060311M30
Thick Film Resistor, 1.33MΩ, 0.063W, 1%	MC0063W060311M33
Thick Film Resistor, 1.4MΩ, 0.063W, 1%	MC0063W060311M40
Thick Film Resistor, 1.5MΩ, 0.063W, 1%	MC0063W060311M50
Thick Film Resistor, 1.54MΩ, 0.063W, 1%	MC0063W060311M54
Thick Film Resistor, 1.6MΩ, 0.063W, 1%	MC0063W060311M60
Thick Film Resistor, 1.62MΩ, 0.063W, 1%	MC0063W060311M62
Thick Film Resistor, 1.69MΩ, 0.063W, 1%	MC0063W060311M69
Thick Film Resistor, 1.78MΩ, 0.063W, 1%	MC0063W060311M78
Thick Film Resistor, 1.8MΩ, 0.063W, 1%	MC0063W060311M80
Thick Film Resistor, 1.87MΩ, 0.063W, 1%	MC0063W060311M87
Thick Film Resistor, 2MΩ, 0.063W, 1%	MC0063W060312M00
Thick Film Resistor, 2.2MΩ, 0.063W, 1%	MC0063W060312M20
Thick Film Resistor, 2.26MΩ, 0.063W, 1%	MC0063W060312M26
Thick Film Resistor, 2.37MΩ, 0.063W, 1%	MC0063W060312M37
Thick Film Resistor, 2.4MΩ, 0.063W, 1%	MC0063W060312M40
Thick Film Resistor, 2.49MΩ, 0.063W, 1%	MC0063W060312M49
Thick Film Resistor, 2.61MΩ, 0.063W, 1%	MC0063W060312M61
Thick Film Resistor, 2.7MΩ, 0.063W, 1%	MC0063W060312M70
Thick Film Resistor, 2.74MΩ, 0.063W, 1%	MC0063W060312M74
Thick Film Resistor, 2.87MΩ, 0.063W, 1%	MC0063W060312M87
Thick Film Resistor, 3MΩ, 0.063W, 1%	MC0063W060313M00
Thick Film Resistor, 3.01MΩ, 0.063W, 1%	MC0063W060313M01

Description	Part Number
Thick Film Resistor, 3.3MΩ, 0.063W, 1%	MC0063W060313M30
Thick Film Resistor, 3.32MΩ, 0.063W, 1%	MC0063W060313M32
Thick Film Resistor, 3.48MΩ, 0.063W, 1%	MC0063W060313M48
Thick Film Resistor, 3.6MΩ, 0.063W, 1%	MC0063W060313M60
Thick Film Resistor, 3.65MΩ, 0.063W, 1%	MC0063W060313M65
Thick Film Resistor, 3.83MΩ, 0.063W, 1%	MC0063W060313M83
Thick Film Resistor, 3.9MΩ, 0.063W, 1%	MC0063W060313M90
Thick Film Resistor, 4.02MΩ, 0.063W, 1%	MC0063W060314M02
Thick Film Resistor, 4.3MΩ, 0.063W, 1%	MC0063W060314M30
Thick Film Resistor, 4.42MΩ, 0.063W, 1%	MC0063W060314M42
Thick Film Resistor, 4.64MΩ, 0.063W, 1%	MC0063W060314M64
Thick Film Resistor, 4.7MΩ, 0.063W, 1%	MC0063W060314M70
Thick Film Resistor, 5.1MΩ, 0.063W, 1%	MC0063W060315M10
Thick Film Resistor, 5.11MΩ, 0.063W, 1%	MC0063W060315M11
Thick Film Resistor, 5.6MΩ, 0.063W, 1%	MC0063W060315M60
Thick Film Resistor, 5.62MΩ, 0.063W, 1%	MC0063W060315M62
Thick Film Resistor, 5.9MΩ, 0.063W, 1%	MC0063W060315M90
Thick Film Resistor, 6.2MΩ, 0.063W, 1%	MC0063W060316M20
Thick Film Resistor, 6.49MΩ, 0.063W, 1%	MC0063W060316M49
Thick Film Resistor, 6.8MΩ, 0.063W, 1%	MC0063W060316M80
Thick Film Resistor, 7.5MΩ, 0.063W, 1%	MC0063W060317M50
Thick Film Resistor, 8.2MΩ, 0.063W, 1%	MC0063W060318M20
Thick Film Resistor, 9.1MΩ, 0.063W, 1%	MC0063W060319M10
Thick Film Resistor, 9.53MΩ, 0.063W, 1%	MC0063W060319M53
Thick Film Resistor, 10MΩ, 0.063W, 1%	MC0063W0603110M0

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO